

SAIB-VSA-3P/250/11-OB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Customisable valve plugs are used frequently in special-purpose machine engineering. Such plugs are used to connect solenoid valves. The valve plugs are available in all standard design types. The range includes the design types A, B Industrial, B acc. to DIN, C Industrial and C acc. to DIN. The valve plugs are available in 3 and 4-pole versions without cables. A flat gasket seal is included which, when screwed on, guarantees IP 65 protection.

General ordering data

| | |
|------------|--|
| Version | Field attachable connector, Valve plug, Socket, angled |
| Order No. | 1873090000 |
| Type | SAIB-VSA-3P/250/11-OB |
| GTIN (EAN) | 4032248495368 |
| Qty. | 1 pc(s). |

SAIB-VSA-3P/250/11-OB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|------|
| Net weight | 26 g |
|------------|------|

Technical data customisable plug-in connectors

| | | | | |
|---|---------------------|-------------------|--------------------------------|-----------------------------------|
| All valve plugs are fitted with protective circuits | | Without circuitry | Cable diameter | 6...8 mm (PG9) / 8...10 mm (PG11) |
| Cable diameter, max. | 10 mm | | Cable diameter, min. | 8 mm |
| Cable glands | PG 11 | | Coding | Design A (18 mm) |
| Conductor cross-section, max. | 1.5 mm ² | | Conductor cross-section, min. | 0.34 mm ² |
| Connection cross-section, max. | 1.5 mm ² | | Connection cross-section, min. | 0.34 mm ² |
| Contact surface | Ni | | Housing main material | PA 6 GF |
| Insulation strength | 10 ⁸ Ω | | LED | No |
| Number of poles | 3 | | Plugging cycles | ≤ 50 |
| Pollution severity | 3 | | Protection degree | IP65 |
| Rated current | 10 A | | Rated voltage | 250 V |
| Temperature range of housing | -25...+85 °C | | Type of connection | Screw connection |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002062 | ETIM 7.0 | EC003623 |
| ETIM 8.0 | EC003623 | ETIM 9.0 | EC003623 |
| ECLASS 9.0 | 27-44-01-05 | ECLASS 9.1 | 27-44-01-05 |
| ECLASS 10.0 | 27-44-01-05 | ECLASS 11.0 | 27-44-01-05 |
| ECLASS 12.0 | 27-44-01-05 | ECLASS 13.0 | 27-44-01-05 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | ebf89fc8-a87f-4691-b87a-dfb9921774b4 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |