

ET S7-400-TU-A4-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The ET S7 DIN-A4 non-adhesive labels are used to label the S300, S400 and S7 modules from Siemens. Customised laser printing is possible using Weidmüller's M-Print® Pro software.

- Background colours yellow or turquoise with black printing (boxes)
- Labels can be easily separated (not adhesive)

General ordering data

| | |
|------------|--|
| Version | LaserMark, Device markers, 251 x 11.5 mm, Siemens, Turquoise |
| Order No. | 1865470000 |
| Type | ET S7-400-TU-A4-1 |
| GTIN (EAN) | 4032248434145 |
| Qty. | 10 pc(s). |

ET S7-400-TU-A4-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.1 mm | Depth (inches) | 0.004 inch |
| Height | 251 mm | Height (inches) | 9.882 inch |
| Width | 11.5 mm | Width (inches) | 0.453 inch |
| Net weight | 32.5 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|--------------------------------------|---|-------------|--|
| Application/manufacture | Siemens | | |
| Approval acc. to UL 969 | No | | |
| Colour | Turquoise | | |
| Halogen | Yes | | |
| Material | Vinyl film | | |
| Number of markers per combination | 1 Label sheet = 14 Device markers | | |
| Number of markers per packaging unit | Number of combinations per packaging unit | 10 | |
| | Number of markers per combination | 14 | |
| | Form of supply | Label sheet | |
| Number of markers per packaging unit | 140 | | |
| Number per sheet | 14 | | |
| Operating temperature range | -40...80 °C | | |
| Operating temperature range, max. | 80 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Printing method | Laser print | | |
| UL 94 flammability rating | HB | | |
| Width | 11.5 mm | | |

Device markers

| | |
|---------|-----|
| Halogen | Yes |
|---------|-----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

ET S7-400-TU-A4-1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

