

CLI C 02-3 WS/SW - CD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, white
Order No.	1869821740
Type	CLI C 02-3 WS/SW - CD
GTIN (EAN)	4032248446803
Qty.	500 pc(s).
Alternative product	1568249999

CLI C 02-3 WS/SW - CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3.5 mm	Depth (inches)	0.138 inch
Height	3 mm	Height (inches)	0.118 inch
Width	3.4 mm	Width (inches)	0.134 inch
Net weight	0.04 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

General data

Colour	white	
Colour of printing	black	
Halogen	Yes	
Material	PVC, soft, without Cadmium	
Material colour according to resistance code	9	
Number of markers per combination	1 Reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Reel
Operating temperature range	-30...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-30 °C	
Orientation of print	horizontal	
Printed characters	Symbols	
Printing	-	
Printing method	hot-embossing	
Recommended industries	Process, Machinery	
Type of printing	Standard	
UL 94 flammability rating	V-0	
Version	CD	
Width	3.4 mm	

Conductor and cable markers

Conductor O.D.	1.3 - 3 mm	Conductor O.D., max.	3 mm
Conductor O.D., min.	1.3 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.2 mm ²	Cross-section for connected wire	0.2 - 1.5 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Creation date July 14, 2024 11:06:13 PM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

CLI C 02-3 WS/SW - CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Product Change Notification

[PCN CableLine_DE](#)

[PCN CableLine_EN](#)

Catalogues

[Catalogues in PDF-format](#)

CLI C 02-3 WS/SW - CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration