

CLI M 2-6 GE/SW L2 CD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 6 x 11.3 mm, yellow
Order No.	1871781729
Type	CLI M 2-6 GE/SW L2 CD
GTIN (EAN)	4032248452088
Qty.	250 pc(s).

CLI M 2-6 GE/SW L2 CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	6 mm	Height (inches)	0.236 inch
Width	11.3 mm	Width (inches)	0.445 inch
Net weight	0.244 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

General data

Colour	yellow
Colour of printing	black
Halogen	Yes
Material	PVC, soft, without Cadmium
Material colour according to resistance code	4
Number of markers per combination	1 Reel = Conductor and cable markers
Number of markers per packaging unit	Form of supply Reel
Operating temperature range	-30...80 °C
Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C
Orientation of print	horizontal
Printed characters	Mixed characters
Printing	L2
Printing method	hot-embossing
Recommended industries	Process, Machinery
Type of printing	Standard
UL 94 flammability rating	V-0
Version	CD
Width	11.3 mm

Conductor and cable markers

Conductor O.D.	10 - 317 mm	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 500 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

CLI M 2-6 GE/SW L2 CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Downloads

Product Change Notification	PCN CableLine_DE PCN CableLine_EN
Catalogues	Catalogues in PDF-format

CLI M 2-6 GE/SW L2 CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration