


**CLI C 1-9 GE/SW 480-499 2-PAG RL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 2.5 - 5 mm, 9 x 4.2 mm, yellow |
| Order No.  | <a href="#">1878260480</a>   |
| Type       | CLI C 1-9 GE/SW 480-499 2-PAG RL                                       |
| GTIN (EAN) | 4032248470013  |
| Qty.       | 1,000 pc(s).   |

## CLI C 1-9 GE/SW 480-499 2-PAG RL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 5 mm    | Depth (inches)  | 0.197 inch |
| Height     | 9 mm    | Height (inches) | 0.354 inch |
| Width      | 4.2 mm  | Width (inches)  | 0.165 inch |
| Net weight | 0.157 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|  |  |                |
|--|--|----------------|
| Colour                                       | yellow   |                |
| Colour of printing                           | black  |                |
| Halogen                                      | Yes  |                |
| Insulation cross-section, max.               | 5  |                |
| Material                                     | PVC, soft, without Cadmium                     |                |
| Material colour according to resistance code | 4  |                |
| Number of markers per combination            | 1 Component part = Conductor and cable markers |                |
| Number of markers per packaging unit         | Form of supply                                 | Component part |
| Operating temperature range                  | -30...80 °C                                    |                |
| Operating temperature range, max.            | 80 °C  |                |
| Operating temperature range, min.            | -30 °C   |                |
| Orientation of print                         | horizontal                                     |                |
| Printed characters                           | Numbers  |                |
| Printing method                              | hot-embossing                                  |                |
| Recommended industries                       | Process, Machinery                             |                |
| Type of printing                             | Standard                                       |                |
| UL 94 flammability rating                    | V-0  |                |
| Width  | 4.2 mm   |                |

## Conductor and cable markers

|                               |                     |                                  |                         |
|-------------------------------|---------------------|----------------------------------|-------------------------|
| Conductor O.D.                | 2.5 - 5 mm          | Conductor O.D., max.             | 5 mm                    |
| Conductor O.D., min.          | 2.5 mm              | Conductor cross-section, max.    | 4 mm <sup>2</sup>       |
| Conductor cross-section, min. | 1.5 mm <sup>2</sup> | Cross-section for connected wire | 1.5 - 4 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                         |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

## Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### CLI C 1-9 GE/SW 480-499 2-PAG RL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Product Change Notification

[PCN CableLine\\_DE](#)

[PCN CableLine\\_EN](#)

Catalogues

[Catalogues in PDF-format](#)

**CLI C 1-9 GE/SW 480-499 2-PAG RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



Similar to illustration