

**SAIS-5/7-ZF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

Tension-clamp connection delivers excellent functional security and reduced installation times. With this technology the conductor is plugged into the tension clamp without a wire-end ferrule (optionally with wire-end ferrule). The connection between the conductor and tension clamp is vibration-resistant and boasts long-term stability.

**General ordering data**

Version	Field attachable connector, M12, pin, straight
Order No.	<a href="#">1906390000</a>
Type	SAIS-5/7-ZF
GTIN (EAN)	4032248539383
Qty.	1 pc(s).

## SAIS-5/7-ZF

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	20 g
------------	------

## Technical data customisable plug-in connectors

Cable diameter, max.	6 mm	Cable diameter, min.	4 mm
Coding	A-coded	Conductor cross-section, max.	0.5 mm <sup>2</sup>
Conductor cross-section, min.	0.14 mm <sup>2</sup>	Contact surface	Gold-plated
Housing main material	PA	Insulation strength	10 <sup>8</sup> Ω
Number of poles	5	Plugging cycles	≥ 100
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	60 V
Shield connection	No	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Tension-clamp connection

## General Info

Number of poles	5	Connection 1	M12
Connection 2	Tension-clamp	Housing main material	PA
Connection thread	M12	Contact surface	Gold-plated
Protection degree	IP67	Plugging cycles	≥ 100

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02
ECLASS 14.0	27-44-01-16		

## Environmental Product Compliance

REACH SVHC	Imidazolidine-2-thione 96-45-7
SCIP	a2cb82cf-1eab-43cd-bafb-63d26622fe9e
RoHS Compliance Status	Compliant without exemption

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

Creation date October 5, 2024 5:40:30 AM CEST

Catalogue status 28.09.2024 / We reserve the right to make technical changes.

## SAIS-5/7-ZF

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

**Pole scheme**

