

VG M40-1/MS68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG MS (standard brass cable gland), Cable glands, straight, M 40, 9 mm, OD min. 19 - OD max. 28 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated
Order No.	1909940000
Type	VG M40-1/MS68
GTIN (EAN)	4032248536863
Qty.	10 pc(s).

VG M40-1/MS68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	43.5 mm	Height (inches)	1.713 inch
Length	52.5 mm	Length (inches)	2.067 inch
Net weight	76.1 g		

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (GERML-LOYD)	E-14047
Certificate no. cable gland (UL)	E-199260	Certificate no. cable gland (cULus)	E-199260

General information

AF size	43 mm	AF size 1	43 mm
AF size 2	43 mm	Cable glands	metric, M 40
Clamp insert	Polyamide	External thread	M 40
Halogen	Yes	Length of thread	9 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	28 mm	Outer cable diameter, min.	19 mm
Pitch of thread	1.5 mm	Protection class (UL)	Type 4X
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Seal insert	CR	Sealing	NBR
Tightening torque	12 Nm	Torque for cap nut, max.	18 Nm
Torque for cap nut, min.	16 Nm	Torque for connecting adapter, max.	12.5 Nm
Torque for connecting adapter, min.	11.5 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

Approvals



ROHS	Conform
------	---------

Creation date July 16, 2024 7:50:22 AM CEST

Catalogue status 13.07.2024 / We reserve the right to make technical changes.

VG M40-1/MS68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity - Standard brass nickel plated cable gland - DE PS2480 210608 003ISS00
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	