

VT-TM 1/18 TWIN HF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

TM/HF Twin double-sided labelling: 0.22 – 2.5 mm².
Twin sleeves enable double-sided marking of a conductor. The sleeves can hold two TM-I 18 tags so that, for example, the input and output designations of a cable can be read at one position. The transparent, halogen-free sleeves can be used on conductors with an outside diameter of 1.3 to 4.0 mm.

General ordering data

Version	TM, Socket x 5 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 2.4 - 4 mm
Order No.	1891790000
Type	VT-TM 1/18 TWIN HF
GTIN (EAN)	4032248504534
Qty.	1,000 pc(s).

VT-TM 1/18 TWIN HF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	12 mm	Depth (inches)	0.472 inch
Height	18 mm	Height (inches)	0.709 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	0.15 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Colour	Transparent	Halogen	No
Material	Polyethylene LD	Operating temperature range	-40...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Recommended industries	Transportation, Machinery	Type of printing	neutral
UL 94 flammability rating	HB	Width	5 mm

Conductor and cable markers

Conductor O.D.	2.4 - 4 mm	Conductor O.D., max.	4 mm
Conductor O.D., min.	2.4 mm	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	1.5 mm ²	Cross-section for connected wire	1.5 - 2.5 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Catalogues	Catalogues in PDF-format