

QL 10 WTL 6/4 FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

General ordering data

Version	Cross-connector (terminal), when screwed in, Number of poles: 10, Pitch in mm (P): 11.00, Insu- lated: No, 41 A, Silver grey
Order No.	1897090000
Type	QL 10 WTL 6/4 FF
GTIN (EAN)	4032248514069
Qty.	100 pc(s).

QL 10 WTL 6/4 FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	6 mm	Depth (inches)	0.236 inch
Height	107.8 mm	Height (inches)	4.244 inch
Width	2 mm	Width (inches)	0.079 inch
Net weight	8.24 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	CuSn	Colour	Silver grey
----------	------	--------	-------------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	11 mm
-----------------	-------

General

Installation advice	Feed-through (bushing), Direct mounting	Number of poles	10
---------------------	---	-----------------	----

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	CAT 1 TERM 16/17 EN