

LM MT300 202/12 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

| | |
|------------|--|
| Version | LaserMark, Device markers, 12 x 202 mm, yellow |
| Order No. | 1915320000 |
| Type | LM MT300 202/12 GE |
| GTIN (EAN) | 4032248547968 |
| Qty. | 10 pc(s). |

LM MT300 202/12 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.08 mm | Depth (inches) | 0.003 inch |
| Height | 12 mm | Height (inches) | 0.472 inch |
| Width | 202 mm | Width (inches) | 7.953 inch |
| Net weight | 12.8 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

General data

| | | |
|--|---|-------------|
| Adhesive | Acrylate adhesive | |
| Approval acc. to UL 969 | Yes | |
| Colour | yellow | |
| Halogen | No | |
| Material | Polyester, PVC-free | |
| Material colour according to resistance code | 4 | |
| Number of markers per combination | 1 Label sheet = 22 Device markers | |
| Number of markers per packaging unit | Form of supply | Label sheet |
| | Number of markers per combination | 22 |
| | Number of combinations per packaging unit | 10 |
| Number of markers per packaging unit | 220 | |
| Number per sheet | 22 | |
| Operating temperature range | -40...150 °C | |
| Operating temperature range, max. | 150 °C | |
| Operating temperature range, min. | -40 °C | |
| Printing method | Laser print | |
| UL 94 flammability rating | HB | |
| Version | Self-adhesive | |
| Width | 202 mm | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

LM MT300 202/12 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

