

**SAIL-M12GM8W-3-1.5V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

**General ordering data**

|            |   |
|------------|---|
| Version    | Sensor/actuator line, Connecting line, M12 / M8, Number of poles : 3, 1.5 m, pin, straight - socket, 90&deg;, Shielded: No, LED: No, Sheath material: PVC, Halogen: Yes |
| Order No.  | <a href="#">1938180150</a>  |
| Type       | SAIL-M12GM8W-3-1.5V   |
| GTIN (EAN) | 4032248611638   |
| Qty.       | 1 pc(s).  |

**SAIL-M12GM8W-3-1.5V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |      |
|------------|------|
| Net weight | 67 g |
|------------|------|

**Technical specifications for cable**

|  |                      |                           |                      |
|--|----------------------|---------------------------|----------------------|
| Cable length                                   | 1.5 m                | Colour coding             | brown, blue, black   |
| Configurable cable length                      | No                   | Core cross-section        | 0.25 mm <sup>2</sup> |
| Halogen  | Yes                  | Insulation                | PVC                  |
| Irradiation crosslinked                        | No                   | Number of poles           | 3                    |
| Outer cladding in accordance with UL AWM style | 2464 (80 °C / 300 V) | Outside diameter          | 4.5 mm ± 0.2 mm      |
| Resistant to welding beads                     | No                   | Sheath material           | PVC                  |
| Sheathing colour                               | black                | Shielded                  | No                   |
| Suitable for cable carriers                    | No                   | Temperature range, moving | -5...80 °C           |
| Temperature range, stationary                  | -30...80 °C          | Torsion resistance        | 0 °/m                |
| Welding spark resistance                       | No                   |                           |                      |

**General technical data**

|                              |                                     |                        |   |
|------------------------------|-------------------------------------|------------------------|---|
| AF size                      | 12 mm                               | Coding                 | M12 = A-coded, M8 = none                      |
| Connection thread            | M12 / M8                            | Contact surface        | Gold-plated                                   |
| Housing main material        | PUR                                 | Insulation strength    | 10 <sup>8</sup> Ω                             |
| LED                          | No                                  | Plugging cycles        | ≥ 100   |
| Pollution severity           | 3                                   | Protection degree      | IP65, IP66, IP67, IP68, IP69, when screwed in |
| Rated current                | 4 A                                 | Rated voltage          | 60 V  |
| Temperature range of housing | -25...+85 °C                        | Threaded ring material | Diecast zinc                                  |
| Tightening torque            | M8: 0.5 - 0.6 Nm, M12: 0.8 - 1.2 Nm | Version                | pin, straight - socket, 90°                   |
| jumpered                     | No                                  |                        |   |

**Electrical properties**

|                     |                   |               |      |
|---------------------|-------------------|---------------|------|
| Insulation strength | 10 <sup>8</sup> Ω | Rated voltage | 60 V |
|---------------------|-------------------|---------------|------|

**General standards**

|                    |                                  |
|--------------------|----------------------------------|
| Connector standard | IEC 61076-2-101, IEC 61076-2-104 |
|--------------------|----------------------------------|

**Standards**

|                    |                                  |
|--------------------|----------------------------------|
| Connector standard | IEC 61076-2-101, IEC 61076-2-104 |
|--------------------|----------------------------------|

**Plug, left**

|           |   |
|-----------|---|
| Plug left | M12, A-coded, IP69, male contact, straight, Plastic, unshielded |
|-----------|---|

**Plug, right**

|            |  |
|------------|--|
| Plug right | M8, IP69, female contact, angled 90°, Plastic, LED, unshielded |
|------------|--|

Creation date July 15, 2024 12:43:16 PM CEST

**SAIL-M12GM8W-3-1.5V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001855    | ETIM 7.0    | EC001855    |
| ETIM 8.0    | EC001855    | ETIM 9.0    | EC001855    |
| ECLASS 9.0  | 27-06-03-11 | ECLASS 9.1  | 27-06-03-11 |
| ECLASS 10.0 | 27-06-03-11 | ECLASS 11.0 | 27-06-03-11 |
| ECLASS 12.0 | 27-06-03-11 | ECLASS 13.0 | 27-06-03-11 |

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 1c533b66-fcff-4da5-b89f-fd55fbf5cb55 |
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                             |   |
|-----------------------------|---|
| Product Change Notification | <a href="#">DE - Technische Änderung zu M12 Gewinding mit 6-Kant</a><br><a href="#">EN - Technical change to M12 nut with additional hexagonal mounting</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>  |
| Brochures                   | <a href="#">FL FIELDWIRING EN</a><br><a href="#">FL FIELDWIRING EN</a>  |

**SAIL-M12GM8W-3-1.5V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**
**Dimensioned drawing**


Male, straight

**Pole scheme**

**Wiring diagram**

**Dimensioned drawing**


Angled socket

**Pole scheme**

**The ideal tool: Screwty® with torque function**

Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F