



**BCZ 3.81/12/90F SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
- Flange with screw (F)
- Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.

**General ordering data**

|              |   |
|--------------|---|
| Version      | PCB plug-in connector, female plug, 3.81 mm, Number of poles: 12, 90°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box |
| Order No.    | <a href="#">1940080000</a>  |
| Type         | BCZ 3.81/12/90F SN OR BX  |
| GTIN (EAN)   | 4032248656745   |
| Qty.         | 50 pc(s).   |
| Product data | IEC: 320 V / 17.5 A / 0.2 - 1.5 mm²<br>UL: 300 V / 10 A / AWG 28 - AWG 16   |
| Packaging    | Box   |

## BCZ 3.81/12/90F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 19.1 mm  | Depth (inches)  | 0.752 inch |
| Height     | 10.5 mm  | Height (inches) | 0.413 inch |
| Width      | 56.14 mm | Width (inches)  | 2.21 inch  |
| Net weight | 11.74 g  |                 |            |

## System Parameters

|  |                                     |                   |              |
|--|-------------------------------------|-------------------|--------------|
| Product family                               | OMNIMATE Signal - series BC/SC 3.81 |                   |              |
| Type of connection                           | Field connection                    |                   |              |
| Wire connection method                       | Clamping yoke connection            |                   |              |
| Pitch in mm (P)                              | 3.81 mm                             |                   |              |
| Pitch in inches (P)                          | 0.15 "                              |                   |              |
| Conductor outlet direction                   | 90°                                 |                   |              |
| Number of poles                              | 12                                  |                   |              |
| L1 in mm                                     | 41.91 mm                            |                   |              |
| L1 in inches                                 | 1.65 "                              |                   |              |
| Number of rows                               | 1                                   |                   |              |
| Pin series quantity                          | 1                                   |                   |              |
| Rated cross-section                          | 1 mm <sup>2</sup>                   |                   |              |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch              |                   |              |
| Touch-safe protection acc. to DIN VDE 0470   | IP20 plugged/ IP10 unplugged        |                   |              |
| Protection degree                            | IP20                                |                   |              |
| Volume resistance                            | ≤5 mΩ                               |                   |              |
| Can be coded                                 | Yes                                 |                   |              |
| Stripping length                             | 7 mm                                |                   |              |
| Clamping screw                               | M 2                                 |                   |              |
| Screwdriver blade                            | 0.4 x 2.5                           |                   |              |
| Screwdriver blade standard                   | DIN 5264                            |                   |              |
| Plugging cycles                              | 25                                  |                   |              |
| Plugging force/pole, max.                    | 7 N                                 |                   |              |
| Pulling force/pole, max.                     | 5 N                                 |                   |              |
| Tightening torque                            | Torque type                         | Wire connection   |              |
|  | Usage information                   | Tightening torque | min. 0.2 Nm  |
|  |                                     |                   | max. 0.25 Nm |
|  | Torque type                         | Screw flange      |              |
|  | Usage information                   | Tightening torque | min. 0.15 Nm |
|  |                                     |                   | max. 0.2 Nm  |

## Material data

|                                       |                               |                                       |        |
|---------------------------------------|-------------------------------|---------------------------------------|--------|
| Insulating material                   | PA 66 GF 30                   | Colour                                | orange |
| Colour chart (similar)                | RAL 2000                      | Insulating material group             | II     |
| Comparative Tracking Index (CTI)      | ≥ 550                         | UL 94 flammability rating             | V-0    |
| Contact material                      | Cu-alloy                      | Contact surface                       | tinned |
| Layer structure of plug contact       | 0.5...1.5 µm Cu / 2...5 µm Sn | Storage temperature, min.             | -40 °C |
| Storage temperature, max.             | 70 °C                         | Operating temperature, min.           | -50 °C |
| Operating temperature, max.           | 120 °C                        | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 120 °C                        |                                       |        |

## Conductors suitable for connection

|                      |                      |
|----------------------|----------------------|
| Clamping range, min. | 0.08 mm <sup>2</sup> |
|----------------------|----------------------|

Creation date July 3, 2024 6:13:56 PM CEST

## BCZ 3.81/12/90F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|   |  |                              |                         |      |
|---|--|------------------------------|-------------------------|------|
| Clamping range, max.                            | 1.5 mm <sup>2</sup>  |                              |                         |      |
| Wire connection cross section AWG, min.         | AWG 28   |                              |                         |      |
| Wire connection cross section AWG, max.         | AWG 16   |                              |                         |      |
| Solid, min. H05(07) V-U                         | 0.2 mm <sup>2</sup>  |                              |                         |      |
| Solid, max. H05(07) V-U                         | 1.5 mm <sup>2</sup>  |                              |                         |      |
| Flexible, min. H05(07) V-K                      | 0.2 mm <sup>2</sup>  |                              |                         |      |
| Flexible, max. H05(07) V-K                      | 1.5 mm <sup>2</sup>  |                              |                         |      |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.2 mm <sup>2</sup>  |                              |                         |      |
| w. plastic collar ferrule, DIN 46228 pt 4, max. | 1.5 mm <sup>2</sup>  |                              |                         |      |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 0.2 mm <sup>2</sup>  |                              |                         |      |
| w. wire end ferrule, DIN 46228 pt 1, max.       | 1.5 mm <sup>2</sup>  |                              |                         |      |
| Plug gauge in accordance with EN 60999 a x b; ø | 2.4 mm x 1.5 mm  |                              |                         |      |
| Clampable conductor                             | Cross-section for conductor connection   | Type                         | fine-wired              |      |
|   |  | nominal                      | 0.5 mm <sup>2</sup>     |      |
|   | wire end ferrule   | Stripping length             | nominal                 | 6 mm |
|   |  | Recommended wire-end ferrule | <a href="#">H0.5/6</a>  |      |
|   | Cross-section for conductor connection   | Type                         | fine-wired              |      |
|   |  | nominal                      | 0.75 mm <sup>2</sup>    |      |
|   | wire end ferrule   | Stripping length             | nominal                 | 6 mm |
|   |  | Recommended wire-end ferrule | <a href="#">H0.75/6</a> |      |
|   | Cross-section for conductor connection   | Type                         | fine-wired              |      |
|   |  | nominal                      | 1 mm <sup>2</sup>       |      |
|   | wire end ferrule   | Stripping length             | nominal                 | 6 mm |
|   |  | Recommended wire-end ferrule | <a href="#">H1.0/6</a>  |      |
|   | Cross-section for conductor connection   | Type                         | fine-wired              |      |
|   |  | nominal                      | 1.5 mm <sup>2</sup>     |      |
|   | wire end ferrule   | Stripping length             | nominal                 | 7 mm |
|   |  | Recommended wire-end ferrule | <a href="#">H1.5/7</a>  |      |
| Reference text                                  | The outside diameter of the plastic collar should not be larger than the pitch (P), Length of ferrules is to be chosen depending on the product and the rated voltage. |                              |                         |      |

## Rated data acc. to IEC

|   |                        |   |                  |
|---|------------------------|---|------------------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=20°C)                             | 15.9 A                 | Rated current, min. number of poles (Tu=40°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=40°C)                             | 14.1 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 76 A |

**BCZ 3.81/12/90F SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Rated data acc. to CSA**

Institute (CSA)



Certificate No. (CSA)

200039-1121690

|                                   |  |
|-----------------------------------|--|
| Rated voltage (Use group B / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 8 A  |
| Wire cross-section, AWG, min.     | AWG 28   |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |

|                                   |        |
|-----------------------------------|--------|
| Rated voltage (Use group C / CSA) | 50 V   |
| Rated current (Use group C / CSA) | 8 A    |
| Wire cross-section, AWG, max.     | AWG 16 |

**Rated data acc. to UL 1059**

Institute (cURus)



Certificate No. (cURus)

E60693

|                                       |  |
|---------------------------------------|--|
| Rated voltage (Use group B / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 28   |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |

|                                       |        |
|---------------------------------------|--------|
| Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, max.         | AWG 16 |

**Packing**

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 165 mm |
| VPE width | 118 mm | VPE height | 46 mm  |

**Type tests**

|  |            |   |
|--|------------|---|
| Test: Durability of markings                 | Standard   | DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96  |
|  | Test       | mark of origin, type identification, rated voltage, rated cross-section, pitch, type of material, approval marking UL, approval marking CSA |
|  | Evaluation | available   |
|  | Test       | durability  |
| Test: Misengagement (Non-interchangeability) | Evaluation | passed  |
|  | Standard   | DIN EN 61984 section 6.3 and 6.9.1 / 09.02, DIN EN 60512-13-5 / 11.06   |
|  | Test       | 180° turned without coding elements   |
|  | Evaluation | passed  |
|  | Test       | visual examination  |
|  | Evaluation | passed  |

## BCZ 3.81/12/90F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|   |                |  |
|---|----------------|--|
| Test: Clampable cross section                             | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02 |
|   | Conductor type | Type of conductor and solid 0.08 mm <sup>2</sup> conductor cross-section           |
|   |                | Type of conductor and stranded 0.08 mm <sup>2</sup> conductor cross-section        |
|   |                | Type of conductor and solid 1.5 mm <sup>2</sup> conductor cross-section            |
|   |                | Type of conductor and stranded 1.5 mm <sup>2</sup> conductor cross-section         |
|   |                | Type of conductor and AWG 28/1 conductor cross-section                             |
|   |                | Type of conductor and AWG 28/19 conductor cross-section                            |
|   |                | Type of conductor and AWG 16/1 conductor cross-section                             |
|   |                | Type of conductor and AWG 16/19 conductor cross-section                            |
|   | Evaluation     | passed   |
| Test for damage to and accidental loosening of conductors | Standard       | DIN EN 60999-1 section 9.4 / 12.00   |
|   | Requirement    | 0.2 kg   |
|   | Conductor type | Type of conductor and stranded 0.25 mm <sup>2</sup> conductor cross-section        |
|   |                | Type of conductor and AWG 28/1 conductor cross-section                             |
|   |                | Type of conductor and AWG 28/19 conductor cross-section                            |
|   | Evaluation     | passed   |
|   | Requirement    | 0.3 kg   |
|   | Conductor type | Type of conductor and solid 0.5 mm <sup>2</sup> conductor cross-section            |
|   |                |  |
|   | Evaluation     | passed   |
|   | Requirement    | 0.4 kg   |
|   | Conductor type | Type of conductor and solid 1.5 mm <sup>2</sup> conductor cross-section            |
|   |                | Type of conductor and stranded 1.5 mm <sup>2</sup> conductor cross-section         |
|   |                | Type of conductor and AWG 16/1 conductor cross-section                             |
|   |                | Type of conductor and AWG 16/19 conductor cross-section                            |
|   | Evaluation     | passed   |

## BCZ 3.81/12/90F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|               |                |   |
|---------------|----------------|---|
| Pull-out test | Standard       | DIN EN 60999-1 section 9.5 / 12.00  |
|               | Requirement    | ≥10 N   |
|               | Conductor type | Type of conductor and stranded 0.25 mm <sup>2</sup> conductor cross-section |
|               |                | Type of conductor and AWG 28/1 conductor cross-section                      |
|               |                | Type of conductor and AWG 28/19 conductor cross-section                     |
|               | Evaluation     | passed  |
|               | Requirement    | ≥20 N   |
|               | Conductor type | Type of conductor and H05V-U0.5 conductor cross-section                     |
|               |                |   |
|               | Evaluation     | passed  |
|               | Requirement    | ≥40 N   |
|               | Conductor type | Type of conductor and H07V-U1.5 conductor cross-section                     |
|               |                | Type of conductor and H07V-K1.5 conductor cross-section                     |
|               |                | Type of conductor and AWG 16/1 conductor cross-section                      |
|               |                | Type of conductor and AWG 16/19 conductor cross-section                     |
|               | Evaluation     | passed  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ECLASS 9.0  | 27-44-03-09 | ECLASS 9.1  | 27-44-03-09 |
| ECLASS 10.0 | 27-44-03-09 | ECLASS 11.0 | 27-46-02-02 |
| ECLASS 12.0 | 27-46-02-02 | ECLASS 13.0 | 27-46-02-02 |

## Environmental Product Compliance

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | ea9dd4b8-c51f-409c-885a-41700372be61 |

## BCZ 3.81/12/90F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Important note

|                |  |
|----------------|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.   |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E60693     |

## Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>  |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL_BASE_STATION_EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


## BCZ 3.81/12/90F SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

## Drawings

## Product image



## Dimensional drawing



## Graph



## Graph



## Graph



## Graph





WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.  
Zu widerhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksunterzeichnung vorbehalten.  
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.  
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. ALL RIGHTS RESERVED IN THE EVENT OF THE GRANT OF A PATENT, UTILITY MODEL OR DESIGN.

BCZ 3.81/.../90 ...



BCZ 3.81/.../90F ...



NOTE:  
n=NO OF POLES  
P=PITCH

KUNDENZEICHNUNG  
CUSTOMER DRAWING

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance with VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|    |         |           |
|----|---------|-----------|
| 16 | 57.15   | 2.250     |
| 15 | 53.34   | 2.100     |
| 14 | 49.53   | 1.950     |
| 13 | 45.72   | 1.800     |
| 12 | 41.91   | 1.650     |
| 11 | 38.10   | 1.500     |
| 10 | 34.29   | 1.350     |
| 9  | 30.48   | 1.200     |
| 8  | 26.67   | 1.050     |
| 7  | 22.86   | 0.900     |
| 6  | 19.05   | 0.750     |
| 5  | 15.24   | 0.600     |
| 4  | 11.43   | 0.450     |
| 3  | 7.62    | 0.300     |
| 2  | 3.81    | 0.150     |
| n  | L1 [mm] | L1 [inch] |

|                              |  |   |  |
|------------------------------|--|---|--|
|                              |  | CAT.NO.: .  |  |
| 62605/5<br>17.08.12 SHI_S 01 |  | <b>Weidmüller</b>  |  |
| MODIFICATION                 |  | C 40381 03  |  |
| DRAWN 24.02.2006 GU_D        |  | DRAWING NO. ISSUE NO.   |  |
| RESPONSIBLE XU_S             |  | <b>BCZ 3.81/.../90... SN ...</b><br>BUCHSENLEISTE<br>SOCKET BLOCK                                       |  |
| CHECKED 27.08.2012 ZHOU_N    |  |   |  |
| APPROVED XU_S                |  |   |  |
| SCALE: 2/1                   |  | PRODUCT FILE: BCZ 3.81 7070   |  |
| SUPERSEDES: .                |  |   |  |
| SUPERSEDED BY: .             |  |   |  |