

SAIE-M12B-5-1.0U-FP-M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M12, Female socket, straight, Mounting thread: M 16 x 1.5, Number of poles: 5, Strand / cable length: 1 m, Front mounting
Order No.	1963550000
Type	SAIE-M12B-5-1.0U-FP-M16
GTIN (EAN)	4032248645640
Qty.	1 pc(s).

SAIE-M12B-5-1.0U-FP-M16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	38 g
------------	------

Technical data customisable plug-in connectors

Coding	A-coded	Contact surface	Gold-plated
Housing main material	Zinc diecast	Number of poles	5
Plugging cycles	≥ 100	Protection degree	IP67, when screwed in
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	Rated voltage	60 V

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

General data

Cable length	1 m	Coding	A-coded
Conductor O.D.	-	Connection thread	M12
Contact surface	Gold-plated	Core cross-section	0.34 mm ²
Housing main material	Zinc diecast	Material	PVC
Mounting thread	M 16 x 1.5	Number of poles	5
Plugging cycles	≥ 100	Protection degree	IP67, when screwed in
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	Rated voltage	60 V
Rated voltage	250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole)	Strand / cable length	1 m
Type of mounting	Front mounting	Wire cross section (Print/Online)	0.34 (4- and 5-pole)/ 0.25 (8-pole)/ 0.14 (12-pole)

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ETIM 9.0	EC003570
ECLASS 9.0	27-44-01-03	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-03	ECLASS 11.0	27-44-01-03
ECLASS 12.0	27-44-01-03	ECLASS 13.0	27-44-01-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	4060c755-8d0b-4d43-bdb3-4ffabe9d7497

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

Creation date May 23, 2024 10:05:21 PM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

SAIE-M12B-5-1.0U-FP-M16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)

SAIE-M12B-5-1.0U-FP-M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pole scheme

