

ZQV 1.5N/7 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 7, Pitch in mm (P): 3.50, Insulated: Yes, Width: 23 mm |
| Order No. | 1985630000 |
| Type | ZQV 1.5N/7 BL |
| GTIN (EAN) | 4050118370522 |
| Qty. | 20 pc(s). |

ZQV 1.5N/7 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 2.8 mm | Depth (inches) | 0.11 inch |
| Height | 21.9 mm | Height (inches) | 0.862 inch |
| Width | 23 mm | Width (inches) | 0.906 inch |
| Net weight | 2.185 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|---------------------------|-------|--------|------|
| Material | Wemid | Colour | blue |
| UL 94 flammability rating | V-0 | | |

Additional technical data

| | | | |
|--------------------------|-----|----------------|---------|
| Explosion-tested version | Yes | Type of fixing | Plugged |
|--------------------------|-----|----------------|---------|

Cross-connector

| | | | |
|-----------------------|--------|---------------------------|--------|
| Rated current, 2-pole | 17.5 A | Rated current, multi-pole | 17.5 A |
|-----------------------|--------|---------------------------|--------|

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 3.5 mm |
|-----------------|--------|

General

| | |
|-----------------|---|
| Number of poles | 7 |
|-----------------|---|

Rating data

| | |
|---------------|--------|
| Rated current | 17.5 A |
|---------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Important note

| | |
|---------------------|---|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used |
|---------------------|---|

ZQV 1.5N/7 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

ROHS

Conform

DownloadsApproval/Certificate/Document of Con-
formity[Confirmation of Standards EN 45545-2_2020-10](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[Zuken E3.S](#)

User Documentation

[2434520000_BED-ANL.ZQV_A_REIHE.pdf](#)[StorageConditionsTerminalBlocks](#)[User Manual ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)