


AAP11 6 LO RD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The unique modular concept can be tailored to every type of machine. The potential distribution terminal blocks AAP are successful thanks to their uniform design with two possible constructions – alternating or grouped. In the grouped structure of the control voltage distribution, the potentials are located on different terminal blocks and thus form entire potential blocks.

General ordering data

| | |
|------------|---|
| Version | Supply terminal, PUSH IN, 6 mm ² , 500 V, 41 A, dark beige |
| Order No. | 1989780000 |
| Type | AAP11 6 LO RD |
| GTIN (EAN) | 4050118485097 |
| Qty. | 20 pc(s). |

AAP11 6 LO RD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------------------------|------------|----------------|-----------|
| Depth | 47 mm | Depth (inches) | 1.85 inch |
| Depth including DIN rail | 48 mm | Height | 85.5 mm |
| Height (inches) | 3.366 inch | Width | 8.1 mm |
| Width (inches) | 0.319 inch | Net weight | 15.385 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Material data

| | | | |
|--------------------------------|-------|---------------------------|------------|
| Material | Wemid | Colour | dark beige |
| Colour of operational elements | red | UL 94 flammability rating | V-0 |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX) | TUEV17ATEX8030U | Certificate No. (IECEX) | IECEXTUR17.0015U |
| Max. voltage (ATEX) | 550 V | Current (ATEX) | 33 A |
| Wire cross section max. (ATEX) | 6 mm ² | Max. voltage (IECEX) | 550 V |
| Current (IECEX) | 33 A | Wire cross section max. (IECEX) | 6 mm ² |
| Marking EN 60079-7 | Ex ec II C Gc | Ex 2014/34/EU label | II 2 G D |

System specifications

| | | | |
|-------------------------------|-----|-------------------------------------|-------|
| End cover plate required | Yes | Number of potentials | 1 |
| Number of levels | 1 | Number of clamping points per level | 1 |
| Number of potentials per tier | 1 | Levels cross-connected internally | No |
| PE connection | No | Rail | TS 35 |
| N-function | No | PE function | No |
| PEN function | No | | |

Additional technical data

| | | | |
|--------------------------|---------|---------------------|-------|
| Explosion-tested version | Yes | Installation advice | Rail |
| Open sides | right | Snap-on | No |
| Type of fixing | Snap-on | Type of mounting | TS 35 |
| With snap-in pegs | No | | |

CSA rating data

| | | | |
|-------------------------------|-----------------|-------------------------------|-------|
| Certificate No. (CSA) | 200039-70089609 | Current size B (CSA) | 36 A |
| Current size C (CSA) | 36 A | Voltage size B (CSA) | 300 V |
| Voltage size C (CSA) | 300 V | Wire cross section max. (CSA) | 8 AWG |
| Wire cross section min. (CSA) | 22 AWG | | |

Conductors for clamping (additional connection)

Connection type, additional connection PUSH IN

Conductors for clamping (rated connection)

| | |
|----------------------|----------------------|
| Blade size | 1.0 x 5.5 mm |
| Clamping range, max. | 6 mm ² |
| Clamping range, min. | 0.34 mm ² |

Creation date July 15, 2024 9:31:53 AM CEST

AAP11 6 LO RD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

| | | | |
|---|--|--------------------|----------------------|
| Connection cross-section, stranded, max. | 6 mm ² | | |
| Connection cross-section, stranded, min. | 0.5 mm ² | | |
| Connection direction | top | | |
| Gauge to IEC 60947-1 | A5 | | |
| Number of connections | 1 | | |
| Stripping length | 12 mm | | |
| Tube length for twin wire-end ferrule | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | Tube length | max. | 12 mm |
| | | min. | 10 mm |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |
| | Tube length | max. | 18 mm |
| | | min. | 10 mm |
| | Cross-section for conductor connection | min. | 1 mm ² |
| | | max. | 1.5 mm ² |
| | Tube length | max. | 18 mm |
| | | min. | 12 mm |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Tube length | max. | 12 mm |
| | | min. | 10 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1 mm ² |
| | Tube length | max. | 18 mm |
| | | min. | 10 mm |
| | Cross-section for conductor connection | nominal | 1.5 mm ² |
| | Tube length | max. | 18 mm |
| | | min. | 12 mm |
| | Cross-section for conductor connection | nominal | 2.5 mm ² |
| | Tube length | max. | 18 mm |
| | | min. | 10 mm |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Cross-section for conductor connection | min. | 4 mm ² |
| | | max. | 6 mm ² |
| | Tube length | nominal | 10 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1 mm ² |
| | Tube length | min. | 10 mm |
| | Cross-section for conductor connection | min. | 1.5 mm ² |
| | | max. | 2.5 mm ² |
| | Tube length | max. | 18 mm |
| | | min. | 12 mm |
| | Cross-section for conductor connection | nominal | 4 mm ² |
| | Tube length | max. | 18 mm |
| | | min. | 10 mm |
| Cross-section for conductor connection | min. | 6 mm ² | |
| | max. | 10 mm ² | |
| Twin wire-end ferrules, max. | 1.5 mm ² | | |
| Twin wire-end ferrules, min. | 0.5 mm ² | | |
| Type of connection | PUSH IN | | |
| Wire connection cross section AWG, max. | AWG 8 | | |
| Wire connection cross section AWG, min. | AWG 22 | | |
| Wire connection cross section, finely stranded, max. | 6 mm ² | | |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm ² | | |

AAP11 6 LO RD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

| | |
|---|---------------------|
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² |
|---|---------------------|

| | |
|---|-------------------|
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm ² |
|---|-------------------|

| | |
|---|---------------------|
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² |
|---|---------------------|

| | |
|---|-------------------|
| Wire connection cross-section, solid core, max. | 6 mm ² |
|---|-------------------|

| | |
|---|---------------------|
| Wire connection cross-section, solid core, min. | 0.5 mm ² |
|---|---------------------|

General

| | | | |
|---|----------------------------------|---|-------|
| Installation advice | Rail | Rail | TS 35 |
| Standards | In accordance with IEC 60947-7-1 | Wire connection cross section AWG, max. | AWG 8 |
| Wire connection cross section AWG, min. | AWG 22 | | |

Rating data

| | | | |
|--|-------------------|---------------------------------|----------------------------------|
| Rated cross-section | 6 mm ² | Rated voltage | 500 V |
| Rated DC voltage | 500 V | Rated current | 41 A |
| Current at maximum wires | 41 A | Standards | In accordance with IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 0.78 mΩ | Rated impulse withstand voltage | 6 kV |
| Power loss in accordance with IEC 60947-7-x | 1.31 W | Pollution severity | 3 |
| Surge voltage category | III | | |

UL rating data

| | | | |
|--|--------|--|-------|
| Certificate No. (cURus) | E60693 | Conductor size Factory wiring max. (cURus) | 8 AWG |
| Conductor size Factory wiring min. (cURus) | 22 AWG | Conductor size Field wiring max. (cURus) | 8 AWG |
| Conductor size Field wiring min. (cURus) | 22 AWG | Current size B (cURus) | 36 A |
| Current size C (cURus) | 36 A | Voltage size B (cURus) | 300 V |
| Voltage size C (cURus) | 300 V | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000897 | ETIM 7.0 | EC000897 |
| ETIM 8.0 | EC000897 | ETIM 9.0 | EC000897 |
| ECLASS 9.0 | 27-14-11-20 | ECLASS 9.1 | 27-14-11-20 |
| ECLASS 10.0 | 27-14-11-20 | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-01 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

AAP11 6 LO RD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E60693 |

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | Attestation of Conformity IECEx Certificate ATEX Certificate DNVGL certificate BV certificate CCC Ex Certificate 20-AV4BO-0271U CE Declaration of Conformity UKCA declaration of conformity Confirmation of Standards EN 45545-2_2020-10 |
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| Tender specification | Klippon® Connect 1989780000 DE Klippon® Connect 1989780000 EN |
| User Documentation | NTI AAP11 StorageConditionsTerminalBlocks AAP Terminal Blocks for control voltage distribution User Manual AXC 1.5-16 |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

AAP11 6 LO RD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

