

**WM 2/6 3.5-5.0 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Un-detachable: WM**

Our closed, un-detachable markers are mounted without the need for additional tools. The cable is simply threaded through the openings at both ends before the cables are fixed in position. The inherent tension of the material fixes the marker in place. WM markers are available in four sizes for conductor cross-sections from 0.25mm<sup>2</sup> to 16mm<sup>2</sup>. Each size comes in three label lengths and two colours. This provides you with just the right assortment for carrying out everyday labelling of conductors in a cabinet.

**Your benefits with MultiMark**

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

**General ordering data**

Version	WM, Conductor and cable markers, 3.5 - 5 mm, 17 x 6.4 mm, white
Order No.	<a href="#">2006370000</a>
Type	WM 2/6 3.5-5.0 MM WS
GTIN (EAN)	4050118390186
Qty.	2,000 pc(s).
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

## WM 2/6 3.5-5.0 MM WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.02 inch
Height	17 mm	Height (inches)	0.669 inch
Width	6.4 mm	Width (inches)	0.252 inch
Net weight	0.112 g		

## Temperatures

Operating temperature range	-40...150 °C	Continuous operating temp., min.	-40
Continuous operating temp., max.	150		

## General data

Colour	white	Halogen	No
Material	Polyester	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	7 x 6.4 mm	UL 94 flammability rating	HB
Version	halogen-free	Width	6.4 mm

## Conductor and cable markers

Conductor O.D.	3.5 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	3.5 mm	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	2.5 mm <sup>2</sup>	Cross-section for connected wire	2.5 - 4 mm <sup>2</sup>
Halogen	No	Text field height	6.4 mm
Text field width	7 mm		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### WM 2/6 3.5-5.0 MM WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**WM 2/6 3.5-5.0 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	MULTIMARK ROLLER 115
Order No.	<a href="#">1357420000</a>
GTIN (EAN)	4050118160314
Qty.	1 pc(s).

**Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	RIBBON MM 76/360 SW	Version
Order No.	<a href="#">2005080000</a>	Ink ribbon
GTIN (EAN)	4050118389951	
Qty.	1 pc(s).	

### WM 2/6 3.5-5.0 MM WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	MULTIMARK PLUS ROLLER 1 ...
Order No.	<a href="#">2672590000</a>
GTIN (EAN)	4050118708097
Qty.	1 pc(s).