

ZQV 1.5N/2 RD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 2, Pitch in mm (P): 3.50, Insulated: Yes, Width: 5.5 mm |
| Order No. | 1985650000 |
| Type | ZQV 1.5N/2 RD |
| GTIN (EAN) | 4050118370324 |
| Qty. | 60 pc(s). |

ZQV 1.5N/2 RD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 2.8 mm | Depth (inches) | 0.11 inch |
| Height | 21.9 mm | Height (inches) | 0.862 inch |
| Width | 5.5 mm | Width (inches) | 0.217 inch |
| Net weight | 0.564 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|---------------------------|-------|--------|-----|
| Material | Wemid | Colour | red |
| UL 94 flammability rating | V-0 | | |

Additional technical data

| | | | |
|--------------------------|-----|----------------|---------|
| Explosion-tested version | Yes | Type of fixing | Plugged |
|--------------------------|-----|----------------|---------|

Cross-connector

| | | | |
|-----------------------|--------|---------------------------|--------|
| Rated current, 2-pole | 17.5 A | Rated current, multi-pole | 17.5 A |
|-----------------------|--------|---------------------------|--------|

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 3.5 mm |
|-----------------|--------|

General

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Rating data

| | |
|---------------|--------|
| Rated current | 17.5 A |
|---------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Important note

| | |
|---------------------|---|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used |
|---------------------|---|

ZQV 1.5N/2 RD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Confirmation of Standards EN 45545-2_2020-10 |
|---|--|

| | |
|------------------|---------------------------------|
| Engineering Data | CAD data – STEP |
|------------------|---------------------------------|

| | |
|------------------|----------------------------|
| Engineering Data | Zuken E3.S |
|------------------|----------------------------|

| | |
|--------------------|--|
| User Documentation | 2434520000_BED-ANL.ZQV_A_REIHE.pdf StorageConditionsTerminalBlocks User Manual ZQV 2.5 |
|--------------------|--|

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

| | |
|-----------|--|
| Brochures | |
|-----------|--|