

**CC DIA 30 K MC NE GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

**For custom printing:** Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	ClipCard, Device markers, 30 x 30 mm, Self-adhesive, Ø 30 mm, yellow
Order No.	<a href="#">2047390000</a>
Type	CC DIA 30 K MC NE GE
GTIN (EAN)	4050118411249
Qty.	60 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

**CC DIA 30 K MC NE GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.9 mm	Depth (inches)	0.035 inch
Height	30 mm	Height (inches)	1.181 inch
Width	30 mm	Width (inches)	1.181 inch
Diameter	30 mm	Net weight	1.75 g

**Temperatures**

Operating temperature range	-40...60 °C
-----------------------------	-------------

**General data**

Application/manufacture	Self-adhesive, Ø 30 mm		
Colour	yellow		
Halogen	No		
Material	Polyamide 66		
Number of markers per combination	1 MultiCard = Device markers		
Number of markers per packaging unit	Form of supply	MultiCard	
Operating temperature range	-40...60 °C		
Operating temperature range, max.	60 °C		
Operating temperature range, min.	-40 °C		
UL 94 flammability rating	V-2		
Version	Self-adhesive		
Width	30 mm		

**Device markers**

Diameter	30 mm	Halogen	No
----------	-------	---------	----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Product Change Notification	<a href="#">MultiCard Material modification</a> <a href="#">MultiCard Material Modifikation</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CC DIA 30 K MC NE GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

