

**PAC-S300-SL20-AY1-0M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

With increasing plant complexity, the obsolescence of certain PLCs and the relentless growth in demand for I / O signals, many installations or plants are having to replace existing controllers with new ones, without modifying existing field cabling. With the aid of adapters, pre-assembled cables and interfaces from Weidmüller the problem of replacing one PLC system with another can be solved easily and safely: users can maintain the existing field cabling, test the new system and keep installation downtimes to a minimum.

**General ordering data**

|            |                            |
|------------|----------------------------|
|            |                            |
| Order No.  | <a href="#">2004850005</a> |
| Type       | PAC-S300-SL20-AY1-0M5      |
| GTIN (EAN) | 4099986594081              |
| Qty.       | 1 pc(s).                   |

**PAC-S300-SL20-AY1-0M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |       |
|------------|-------|
| Net weight | 167 g |
|------------|-------|

**Temperatures**

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

**General Data**

|                    |  |                       |                      |
|--------------------|--|-----------------------|----------------------|
| Cable              | Cable LiYY                                 | Cable length          | 0.5 m                |
| Connector PLC side | SIEMENS S7300<br>6ES7921-3AH20-1AA0<br>40P | Interface connector   | 2 x BLC 5.08/10/180R |
| Material           | PVC  | Number of poles, min. | 20-pole              |
| Outer diameter     | 10.15 ± 1 mm                               | Suitable for          | Digital signals      |
| Wire cross-section | 0.5 mm <sup>2</sup>                        |                       |                      |

**Electrical Data**

|   |           |                     |                     |
|---|-----------|---------------------|---------------------|
| Capacity wire / wires                       | 300 pF/m  | High voltage test   | 1 KV/1s             |
| Permissible current strength per path, max. | 2.5 A     | Rated voltage       | ≤ 250 Vdc ≤ 250 Vac |
| Resistance                                  | ≤ 40 mΩ/m | Total current, max. | 10 A                |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ECLASS 9.0  | 27-24-22-20 | ECLASS 9.1  | 27-24-22-20 |
| ECLASS 10.0 | 27-24-22-20 | ECLASS 11.0 | 27-24-22-20 |
| ECLASS 12.0 | 27-24-22-20 | ECLASS 13.0 | 27-24-22-20 |

**Environmental Product Compliance**

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|