

**VP M40 EX SI 7J****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	VPK EX 7J (Ex blanking plug, plastic, 7J), Blanking plug, in closed state, M 40, 18 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">2066760000</a>
Type	VP M40 EX SI 7J
GTIN (EAN)	4050118415452
Qty.	20 pc(s).

## VP M40 EX SI 7J

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	26.5 mm	Height (inches)	1.043 inch
Length	26.5 mm	Length (inches)	1.043 inch
Diameter	40 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	17 mm	Net weight	23.45 g

## Temperatures

Operating temperature	-60 °C...70 °C
-----------------------	----------------

## Certificate numbers cable gland

Approval conditions	ATEX, IECEx	Certificate no. cable gland (ATEX)	IMQ 13 ATEX 010 X
Certificate no. cable gland (IECEx)	IECEx IMQ 13.0003X	Certificate no. cable gland (INMETRO)	TAE00003WV
Identification	Ex eb IIC Gb, Ex tb IIIC Db IP66/68		

## General information

AF size 1	46 mm	Diameter of sealing ring	40 mm
Explosion protection type	Improved safety Ex e	External thread	M 40
Halogen	No	Impact resistance	7 joules in acc. with IEC60079-0
Installation guidelines	See assembly instructions	Length of thread	18 mm
Material	Polyamide 6	O-Ring	Silicone
Operating temperature range, max.	70 °C	Operating temperature range, min.	-60 °C
Pitch of thread	1.5 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Sealing	Silicone
Silicone	Yes	Standards	IEC 60079-0, EN 60079-0, IEC 60079-7, EN 60079-7, EN 60079-31, IEC 60079-31
Torque for connecting adapter, max.	6 Nm	Torque for connecting adapter, min.	6 Nm
Torque for lock nut, max.	6 Nm	Torque for lock nut, min.	5.8 Nm
UL 94 flammability rating	HB		

## Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-35
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

ROHS	Conform
------	---------

### VP M40 EX SI 7J

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

**VP M40 EX SI 7J****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	SKMU M40 MS	Version
Order No.	<a href="#">1737030000</a>	SKMU MS (brass locknut), Locknut, M 40, 5 mm, Brass, nickel-plated
GTIN (EAN)	4008190956509	
Qty.	50 pc(s).	