

AMG CM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Efficient machine and facility operation calls for fail-safe and maintenance-friendly control voltage distribution that can be installed in a time and space-saving manner.

With the new maxGUARD system, the terminal blocks (previously installed separately) for distributing potential to the outputs of the electronic load monitors become an integral part of a 24 V DC control voltage distribution system.

The innovative combination of load monitoring and potential distribution saves time during installation, increases safety against failure and reduces the amount of space required on the terminal rail by 50%.

General ordering data

Version	Control module, 24 V DC
Order No.	2081900000
Type	AMG CM
GTIN (EAN)	4050118419573
Qty.	1 pc(s).

AMG CM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	96.5 mm	Depth (inches)	3.799 inch
Height	125 mm	Height (inches)	4.921 inch
Width	12.2 mm	Width (inches)	0.48 inch
Net weight	56 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
---------------------	----------------	-----------------------	----------------

Input

Current consumption (full load)	225 mA	Current consumption (idle)	25 mA
DC input voltage range	18...30 V DC	Input fuse (internal)	No
Rated input voltage	24 V DC	Surge protection	Suppressor diode
max. admissible residual ripple at the input	100 mVpp		

Output

Connection system	PUSH IN	Surge protection	Suppressor diode
-------------------	---------	------------------	------------------

General data

Conformal coating	No	
Control inputs	ON/ OFF, Reset	
MTTF	According to Standard	SN 29500
	Operating time (hours), min.	3,551,000 h
	Ambient temperature	40 °C
	Input voltage	24 V
	Duty cycle	100 %
Power loss, idling	336 mW	
Power loss, nominal load	452 mW	
Protection degree	IP20	
Relay to activate the output	No	
Surge voltage category	III	

Insulation coordination

Surge voltage category	III
------------------------	-----

Connection data (input)

Conductor cross-section, AWG/kcmil , max.	12 AWG	Conductor cross-section, AWG/kcmil , min.	26 AWG
Conductor cross-section, flexible , min.	0.14 mm ²	Conductor cross-section, rigid , max.	2.5 mm ²
Conductor cross-section, rigid , min.	0.14 mm ²	Number of terminals	2 (Reset / ON)
Screwdriver blade	0.6 x 3.5	Wire connection cross section, flexible (input), max.	2.5 mm ²

AMG CM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data (output)

Conductor cross-section, AWG/kcmil ,
max.

12 AWG

Conductor cross-section, flexible , max.

2.5 mm²

Conductor cross-section, rigid , max.

2.5 mm²

Connection system

PUSH IN

Screwdriver blade

0.6 x 3.5

Conductor cross-section, AWG/kcmil ,
min.

26 AWG

Conductor cross-section, flexible , min.

0.14 mm²

Conductor cross-section, rigid , min.

0.14 mm²

Number of terminals

2 (I</ Alarm)

Connection data (signal)

Wire connection cross-section, flexible
(signal), max.2.5 mm²

Signalling

LED green

Red LED

Load monitoring has dis-
connected, Load monitor-
ing has triggered (flash-
ing), Internal error (rapid
flashing)Operation (failure-free), Ear-
ly warning: I Out > 90% I
Rated (flashing)

Transistor output, positive-switching

Pre-warning, Alarm

Classifications

ETIM 6.0

EC002057

ETIM 8.0

EC002057

ECLASS 9.0

27-37-10-16

ECLASS 10.0

27-37-10-16

ECLASS 12.0

27-37-10-16

ECLASS 14.0

27-37-10-16

ETIM 7.0

EC002057

ETIM 9.0

EC001437

ECLASS 9.1

27-37-10-16

ECLASS 11.0

27-37-10-16

ECLASS 13.0

27-37-10-16

Environmental Product Compliance

REACH SVHC

Lead 7439-92-1

SCIP

a7fff16c-85aa-4fb0-a206-7be03f41b0b7

RoHS Compliance Status

Compliant with exemption

RoHS Exemption (if applicable/known)

7a, 7cl

Approvals

Approvals



ROHS

Conform

UL File Number Search

UL Website

Certificate no. (cULus)

E258476

AMG CM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads


Approval/Certificate/Document of Conformity	MaxGuard AMG ELM UL 508 CSA C22.2.pdf Declaration of Conformity UK Conformity Assessed
Engineering Data	CAD data – STEP
User Documentation	Manual_maxGUARD Operating instructions
Catalogues	Catalogues in PDF-format

AMG CM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Schematic circuit diagram