

UR67-PN-HP-8IOL-12-30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Automation Products - u-remote IP67, Sensor-actuator active distributor, PROFINET V2.3
Order No.	2426250000
Type	UR67-PN-HP-8IOL-12-30M
GTIN (EAN)	4050118434354
Qty.	1 pc(s).

UR67-PN-HP-8IOL-12-30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	30 mm	Height (inches)	1.181 inch
Width	30 mm	Width (inches)	1.181 inch
Length	225 mm	Length (inches)	8.858 inch
Net weight	480 g		

Connections

Fieldbus (BUS-IN)	1x M12 female 4-pole, D-coded	Fieldbus (BUS-OUT)	1x M12 female 4-pole, D-coded
I/O connections	8 x M12 socket 5-pole, A-coded	Supply voltage (AUX-IN)	1x M12 plug 5-pole, L-coded
Supply voltage (AUX-OUT)	1x M12 socket 5-pole, L-coded		

Digital inputs

Diagnostic display	Per channel, via LED, red		
Digital inputs	Short-circuit protection	Yes	
	Overload protection	Yes	
	Reverse polarity protection	Yes	
Input current, high	Type 1 in acc. with IEC 61131-2		
Input current, low	Type 1 in acc. with IEC 61131-2		
Input type	P-switching		
Overload protection	Yes		
Short-circuit protection	Yes		
Status indicator	Per channel, via LED, yellow		

Digital outputs

Diagnostic display	Per channel, via LED, red		
Digital outputs	Short-circuit protection	Yes	
	Overload protection	Yes	
	Reverse polarity protection	Yes	
Max. total current outputs	9 A		
Output voltage, high	max. 2 V		
Output voltage, low	- 1 V		
Overload protection	Yes		
Short-circuit protection	Yes		
Status indicator	Per channel, via LED, yellow		
max. current-carrying capacity per output signal	0.5 A, 2 A		

General data

Housing main material	Zinc diecast	Module variants	IO link, 4 x type A, 4 x type B
Protection degree	IP67	UL 94 flammability rating	UL 94

Supply voltage

Limits	18 V DC ... 30 V DC	Operating voltage	24 V
Power consumption of module electronics	160 mA typical	Reverse polarity protection	Yes

UR67-PN-HP-8IOL-12-30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC001597	ETIM 7.0	EC001597
ETIM 8.0	EC001597	ETIM 9.0	EC001597
ECLASS 9.0	27-24-26-02	ECLASS 9.1	27-24-26-02
ECLASS 10.0	27-24-26-02	ECLASS 11.0	27-24-26-02
ECLASS 12.0	27-24-26-02	ECLASS 13.0	27-24-26-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	82327f13-cd27-455a-ab5b-a62e1996dcf8

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	CE Declaration of Conformity - DE UKCA Declaration of Conformity - EN
Engineering Data	CAD data – STEP
Software	Device description – UR67 - GSDML V2.31 + V.33 / EDS V3.9 / ESI V1.2 files Device description – UR67 - GSDML V2.33 files Device description – UR67 GSDML 1.3
User Documentation	MAN UR67 IO-LINK EN MAN UR67 IO-LINK DE
Catalogues	Catalogues in PDF-format

UR67-PN-HP-8IOL-12-30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	MF 5/10 MC NE WS	Version
Order No.	1954050000	MultiFit, Terminal marker, 5 x 10 mm, Pitch in mm (P): 10.00 Phoenix,
GTIN (EAN)	4032248632923	white
Qty.	250 pc(s).	

angled to straight



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIL-M12WM12G-L-1.5PGR	Version
Order No.	2455320150	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4050118470529	5, 1.5 m, pin, angled - bush straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No

UR67-PN-HP-8IOL-12-30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****straight**

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIL-M12BG-L-1.5PGR	Version
Order No.	2455330150	Sensor/actuator line, One end without connector, M12, Number
GTIN (EAN)	4050118469950	of poles : 5, 1.5 m, Female socket, straight, Shielded: No, LED: No,
Qty.	1 pc(s).	Sheath material: PUR, Halogen: No

angled to angled

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIL-M12WM12W-L-1.5PGR	Version
Order No.	2455300150	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4050118470444	5, 1.5 m, pin, 90° - socket 90°;, Shielded: No, LED: No,
Qty.	1 pc(s).	Sheath material: PUR, Halogen: No

UR67-PN-HP-8IOL-12-30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com**Accessories****Dragline cable Cat.5 PUR - RJ45 IP20 / M12 IP67 straight male**

Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, M12-RJ45

**General ordering data**

Type	IE-C5DD4UG0015MCSA70-E	Version	
Order No.	1044470015		Dragline cable, PROFINET, M12 D-code – IP 67 straight pin, RJ45 IP
GTIN (EAN)	4032248779062		20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 1.5 m
Qty.	1 pc(s).		

Screw connection

M12 plug-in connector in IP 67 available with screw or tension clamp connection

General ordering data

Type	SAISM-4/8S-M12-4P D-COD	Version	
Order No.	1892120000		Field attachable connector, M12, pin, straight
GTIN (EAN)	4032248569380		
Qty.	1 pc(s).		

UR67-PN-HP-8IOL-12-30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****straight to straight**

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIL-M12GM12G-L-1.5PGR	Version
Order No.	2455260150	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4050118470284	5, 1.5 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No

straight to angled

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIL-M12GM12W-L-1.5PGR	Version
Order No.	2455280150	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4050118470369	5, 1.5 m, pin, straight - socket, 90°deg., Shielded: No, LED: No,
Qty.	1 pc(s).	Sheath material: PUR, Halogen: No

UR67-PN-HP-8IOL-12-30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****angled**

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIL-M12BW-L-1.5PGR	Version
Order No.	2455200150	Sensor/actuator line, One end without connector, M12, Number
GTIN (EAN)	4050118470048	of poles : 5, 1.5 m, Socket, angled, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No

straight

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIL-M12G-L-1.5PGR	Version
Order No.	2455220150	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4050118470123	poles : 5, 1.5 m, pin, straight, Shielded: No, LED: No, Sheath material:
Qty.	1 pc(s).	PUR, Halogen: No

UR67-PN-HP-8IOL-12-30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

angled



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIL-M12W-L-1.5PGR	Version
Order No.	2455240150	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4050118470208	poles : 5, 1.5 m, pin, 90°, Shielded: No, LED: No, Sheath material:
Qty.	1 pc(s).	PUR, Halogen: No

M12 straight male - M12 straight male

Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, M12



General ordering data

Type	IE-C5DD4UG0015MCSMCS-E	Version
Order No.	1025950015	Dragline cable, PROFINET, M12 D-code – IP 67 straight pin, M12 D-
GTIN (EAN)	4032248776054	code – IP 67 straight pin, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-
Qty.	1 pc(s).	B), PUR, 1.5 m