

VG M50 EMV-4 MS 30-38**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration**Produktabbildung**

The increasing sensitivity of electronic components and the increasing electromagnetic interference frequencies require cable glands to play an important role in the shielding concept of a system. This type of EMC cable glands are made for shielding against interference frequencies, with a 360° screening connection. A Finger-locking seal provides superior cable retention & strain relief, next to it, the cable gland meets the mechanical requirements of EN 62444. Due to the patented design a very easy and fast assembly will be possible.

General ordering data

Version	VG EMV GEN 4 (EMC cable gland with clamping cage), Cable glands, straight, M 50, 9, OD min. 30 - OD max. 38 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K, Brass, nickel-plated
Order No.	2435200000
Type	VG M50 EMV-4 MS 30-38
GTIN (EAN)	4050118446951
Qty.	5 pc(s).

VG M50 EMV-4 MS 30-38

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	53 mm	Height (inches)	2.087 inch
Length	62 mm	Length (inches)	2.441 inch
Net weight	0.414 g		

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (GERML-LOYD)	E-14047
Certificate no. cable gland (UL)	E199260	Certificate no. cable gland (cULus)	E199260

General information

AF size	58 mm	AF size 1	58 mm
AF size 2	58 mm	Cable glands	metric, M 50
Clamp insert	Polyamide	External thread	M 50
Halogen	Yes	Length of thread	9 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	38 mm	Outer cable diameter, min.	30 mm
Pitch of thread	1.5 mm	Protection class (UL)	Type 4X
Protection degree	IP66, IP68 - 5 bar (30 min.), IP69K	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K
Seal insert	CR	Sealing	NBR
Shield diameter, max.	34 mm	Shield diameter, min.	26 mm
Tightening torque	18 Nm	Torque for cap nut, max.	43 Nm
Torque for cap nut, min.	41 Nm	Torque for connecting adapter, max.	18.5 Nm
Torque for connecting adapter, min.	17.5 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

ROHS	Conform
------	---------

VG M50 EMV-4 MS 30-38

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity - EMC brass nickel plated cable gland - DE PS2480 210608 004ISS00
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

VG M50 EMV-4 MS 30-38**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass nuts for EMC**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU EMV M50	Version
Order No.	1777670000	SKMU MS EMV (brass locknut - EMC), Locknut, M 50, 4.6 mm, Brass,
GTIN (EAN)	4032248157945	nickel-plated
Qty.	10 pc(s).	