

WIL-LBXXXX-W450D024-240SXX0.3BM12GXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its blue light color suitable for special color effects- Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

General ordering data

| | |
|------------|--|
| Order No. | 2436350000 |
| Type | WIL-LBXXXX- W450D024-240SXX0.3BM12GXXXX |
| GTIN (EAN) | 4050118447965 |
| Qty. | 1 pc(s). |

WIL-LBXXXX-W450D024-240SXX0.3BM12GXXXX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 40 mm | Depth (inches) | 1.575 inch |
| Height | 8 mm | Height (inches) | 0.315 inch |
| Width | 240 mm | Width (inches) | 9.449 inch |
| Net weight | 228 g | | |

Temperatures

| | |
|-----------------------|------------|
| Operating temperature | -20 - 60°C |
|-----------------------|------------|

Cable technical specifications

| | | | |
|----------------|-------|--------------------|----------------------|
| Cable Material | PUR | Sheathing colour | black |
| Cable length | 0.3 m | Core cross-section | 0.34 mm ² |

Connection data

| | | | |
|---------|---|-------------------|--------|
| Version | pin, straight | Connection thread | M12 |
| Coding | A-coded | Tightening torque | 0.8 Nm |
| Wiring | Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue) | | |

Electric data

| | | | |
|---------------|---------|---------------|---------|
| Rated voltage | 24 V DC | Rated current | 0.317 A |
| Power | 7.6 W | Dimmable | Yes |

General technical data

| | | | |
|---------------------------------------|--------------|--|---------------------|
| Electronic equipment on rolling stock | No | Recommended class according to UL for use of an power supply | NEC Class 2 |
| Shape of the LED module | Rectangular | Type of connection | Pre-assembled cable |
| Number of LEDs | 42 | Light colour (CCT) | Blue |
| Light current | 98 lm | Emitting angle | 40 ° |
| Spectral colour | 445 - 460 nm | Illumination level | 34 lux |
| Operating life | 60.000 h | Type of mounting | Screw mounting |
| Drill hole spacing | 225 mm | Impact resistance | IK05 |
| Protection degree | IP67 | | |

Material data

| | | | |
|------------------------|-------------------------|------------------------|-----------------------------|
| Housing main material | hard anodised aluminium | Encapsulation compound | PUR V0 |
| Threaded ring material | PA | Material of end caps | Diecast zinc, nickel-plated |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000996 | ETIM 7.0 | EC000996 |
| ETIM 8.0 | EC000996 | ETIM 9.0 | EC000996 |
| ECLASS 9.1 | 27-11-06-35 | ECLASS 10.0 | 27-11-06-35 |
| ECLASS 11.0 | 27-11-06-35 | ECLASS 12.0 | 27-11-06-35 |
| ECLASS 13.0 | 27-11-06-35 | | |

WIL-LBXXXX-W450D024-240SXX0.3BM12GXXXX**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Technical data****Environmental Product Compliance**

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | bf1e8170-69bb-4440-b3e0-4da351a9a3b0 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E354496 |



Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Designation key WIL |
| Catalogues | Catalogues in PDF-format |

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

Detailed drawing



Pole scheme

