


**HS 12.7-38.1/50 MM W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | Conductor and cable markers, 12.7 - 38.1 mm, 50.8 x 60.5 mm, white |
| Order No.          | <a href="#">2437610000</a>   |
| Type               | HS 12.7-38.1/50 MM W   |
| GTIN (EAN)         | 4050118460490  |
| Qty.               | 100 pc(s).   |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a>              |

## HS 12.7-38.1/50 MM W

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.77 mm | Depth (inches)  | 0.03 inch  |
| Height     | 50.8 mm | Height (inches) | 2 inch     |
| Width      | 60.5 mm | Width (inches)  | 2.382 inch |
| Net weight | 6.5 g   |                 |            |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...135 °C |
|-----------------------------|--------------|

### General data

|                                   |              |                                   |   |
|-----------------------------------|--------------|-----------------------------------|---|
| Colour                            | white        | Halogen                           | Yes   |
| Material                          | Polyolefine  | Number per roll                   | 100   |
| Operating temperature range       | -55...135 °C | Operating temperature range, max. | 135 °C  |
| Operating temperature range, min. | -55 °C       | Recommended industries            | Plant manufacture, Energy, Device manufacturer, Machinery |
| Width                             | 60.5 mm      |                                   |   |

### Conductor and cable markers

|                                   |                     |                                  |                           |
|-----------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D.                    | 12.7 - 38.1 mm      | Conductor O.D., max.             | 38.1 mm                   |
| Conductor O.D., min.              | 12.7 mm             | Conductor cross-section, max.    | 240 mm <sup>2</sup>       |
| Conductor cross-section, min.     | 125 mm <sup>2</sup> | Cross-section for connected wire | 125 - 240 mm <sup>2</sup> |
| Halogen                           | Yes                 | Rate of shrinkage                | 3:1                       |
| Recommended shrinking temperature | 90 °C               |                                  |                           |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads


|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|

### HS 12.7-38.1/50 MM W

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**HS 12.7-38.1/50 MM W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |            |
|------------|----------------------------|------------|
| Type       | RIBBON MM-HS 60/300 SW     | Version    |
| Order No.  | <a href="#">2448880000</a> | Ink ribbon |
| GTIN (EAN) | 4050118462944              |            |
| Qty.       | 1 pc(s).                   |            |

**THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | THM MMP ROLLER 115         |
| Order No.  | <a href="#">1357420000</a> |
| GTIN (EAN) | 4050118160314              |
| Qty.       | 1 pc(s).                   |

**HS 12.7-38.1/50 MM W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****THM MULTIMARK PLUS**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | MM PLUS ROLLER 110         |
| Order No.  | <a href="#">2672590000</a> |
| GTIN (EAN) | 4050118708097              |
| Qty.       | 1 pc(s).                   |