

**HS-HF 3.2-6.4/50 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | Conductor and cable markers, 3.2 - 6.4 mm, 50.8 x 10.7 mm, yellow |
| Order No.          | <a href="#">2438070000</a>  |
| Type               | HS-HF 3.2-6.4/50 MM Y   |
| GTIN (EAN)         | 4050118461145   |
| Qty.               | 1,000 pc(s).  |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a>             |

**HS-HF 3.2-6.4/50 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.77 mm | Depth (inches)  | 0.03 inch  |
| Height     | 50.8 mm | Height (inches) | 2 inch     |
| Width      | 10.7 mm | Width (inches)  | 0.421 inch |
| Net weight | 0.6 g   |                 |            |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

**General data**

|                                   |             |                                   |              |
|-----------------------------------|-------------|-----------------------------------|--------------|
| Colour                            | yellow      | Halogen                           | No           |
| Material                          | Polyolefine | Operating temperature range       | -55...105 °C |
| Operating temperature range, max. | 105 °C      | Operating temperature range, min. | -55 °C       |
| Width                             | 10.7 mm     |                                   |              |

**Conductor and cable markers**

|                                   |                     |                                  |                         |
|-----------------------------------|---------------------|----------------------------------|-------------------------|
| Conductor O.D.                    | 3.2 - 6.4 mm        | Conductor O.D., max.             | 6.4 mm                  |
| Conductor O.D., min.              | 3.2 mm              | Conductor cross-section, max.    | 6 mm <sup>2</sup>       |
| Conductor cross-section, min.     | 1.5 mm <sup>2</sup> | Cross-section for connected wire | 1.5 - 6 mm <sup>2</sup> |
| Halogen                           | No                  | Rate of shrinkage                | 2:1                     |
| Recommended shrinking temperature | 90 °C               |                                  |                         |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">NFX 70-100-1 2006 + NF X 70-100-2 2006</a><br><a href="#">BS EN ISO 4589-2 1999</a><br><a href="#">EN 45545-2:2020</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |

### HS-HF 3.2-6.4/50 MM Y

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

