

ACT20P-PRO-FI-AO-DO-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image, Similar to illustration****ACT20P: The flexible solution**

- Precise and highly functional signal converters
- Release levers simplify handling

General ordering data

Version	Frequency signal converter, Limit value monitoring, Frequency, PWM, analogue V / mA, Transistor (Alarm)
Order No.	2447950000
Type	ACT20P-PRO-FI-AO-DO-P
GTIN (EAN)	4050118462128
Qty.	1 pc(s).

ACT20P-PRO-FI-AO-DO-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	113.7 mm	Depth (inches)	4.476 inch
Height	117.2 mm	Height (inches)	4.614 inch
Width	12.5 mm	Width (inches)	0.492 inch
Net weight	999 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...60 °C
Humidity	0...95 % (no condensation)		

Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

Input

Input frequency	0,01 Hz...200 kHz	Input voltage	Threshold voltage (NPN / PNP Sensor): 3 V...43.5 V (configurable), Hysteresis level: ≥0.5 V
Sensor	NPN/PNP sensor, NAMUR sensor, according to EN60947-5-6, switch with or without RS, RP, 2-wire transmitter (without own power supply), 3 wire NPN/PNP-transistor, frequency generator, PDM	Sensor supply	18 V ±15 %, 8.2 V ±15% (@ NAMUR sensor)

Output (digital)

Alarm function	configurable, Top and bottom limit values, window range, Short circuit at input, Alarm delay: 0...10 s, Hysteresis: 10 V	Number of digital outputs	1
Rated switching current	100 mA	Rated switching voltage	24 VDC ±30%
Type	NPN-Transistor, Switching frequency 5 kHz		

Output (analogue)

Load resistance current	≤ 600 Ω	Load resistance voltage	≥ 1 kΩ
Number of analogue outputs	1	Output current	-20...+20 mA, ± 10mA, 0(4)...20 mA, configurable downscale (3.5 mA)/ up-scale (23 mA) @ error
Output voltage	0...5 V, 0(1)...5 V, 0(2)...10 V, -5...+5 V, -10...+10 V	Signal output	direct or inverted
Transmit function	Linear, $x^{1/2}$, $x^{3/2}$, $x^{5/2}$ or user-defined curve (101 points), direct or inverted	Type (analogue output)	Voltage and current output (configurable)

ACT20P-PRO-FI-AO-DO-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General data

Accuracy	$\leq \pm 0.1\%$ of span	Configuration	with push-buttons and display
Long-term drift	$\leq \pm 0.05\%$ of the measurement range / year	Power consumption	$\leq 2.6\text{ W}$
Rail	TS 35	Step response time	40 ms + period
Temperature coefficient	$\leq 0.02\%$ / °C, $\leq 100\text{ ppm/K}$ of final value	Voltage supply	24...230 V DC $\pm 15\%$, 24...230 V AC $\pm 15\%$ @48...62 Hz

Insulation coordination

EMC standards	EN 61326-1	Impulse withstand voltage	5 kV (1.2/50 μs)
Insulation voltage	4 kV _{eff} / 1 min.	Pollution severity	2
Rated voltage	600 V	Surge voltage category	II

Safety-related basic specifications

Safety category	No
-----------------	----

Connection data

Type of connection	PUSH IN
--------------------	---------

Classifications

ETIM 6.0	EC002918	ETIM 7.0	EC002918
ETIM 8.0	EC002918	ETIM 9.0	EC002918
ECLASS 9.0	27-21-01-28	ECLASS 9.1	27-21-01-28
ECLASS 10.0	27-21-01-28	ECLASS 11.0	27-21-01-28
ECLASS 12.0	27-21-01-28	ECLASS 13.0	27-21-01-28

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2f6dd957-421a-46db-a0c2-cf1609156924

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	UL certification DNV certification Bureau Veritas certification IECEx certification Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Configuration manual Instruction sheet
Catalogues	Catalogues in PDF-format





Creation date May 23, 2024 12:06:24 PM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

ACT20P-PRO-FI-AO-DO-P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings
Connection diagram

Dimensioned drawing

Flow diagram part

Measuring overrange


ACT20P-PRO-FI-AO-DO-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 8/13.5/43.3 SAI AU	Version
Order No.	1912130000	ESG, Device markers x 13.5 mm, PA 66, Colour: Transparent
GTIN (EAN)	4032248541164	
Qty.	5 pc(s).	

ACT20P-PRO-FI-AO-DO-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.



General ordering data

Type	ESG 6.6/11 BHZ 5.00/02	Version
Order No.	1082490000	ESG, Device markers x 11 mm, PA 66, Colour: white
GTIN (EAN)	4032248845330	
Qty.	200 pc(s).	

ACT20P-PRO-FI-AO-DO-P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings


PUSH IN technology

