

HDC XX6A01 MFSXXXX-4000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Version	Data use
Order No.	2453544000
Type	HDC XX6A01 MFSXXXX-4000
GTIN (EAN)	4050118467642
Qty.	1 pc(s).

HDC XX6A01 MFSXXXX-4000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.01 g
------------	--------

Temperatures

Limit temperature	-40 °C ... 90 °C
-------------------	------------------

General data

Cable length	40 m	Category	Cat. 6A
Coding	X-coded	Contact surface	Au (Gold)
Insulation strength	$\geq 10^8 \Omega$	Module side version	Male
Number of poles	8	Opposite side version	Female, straight
Plugging cycles	\u2265 100	Pollution severity	2
Rated current	0.5 A	Rated voltage	50 V
Transmission rate	10 Gbps, 10 Gbit/s	Type	Pin

Cable technical specifications

Cable length	40 m	
Colour coding	white / orange, orange, white / green, green, white / brown, brown, white / blue, blue	
Halogen	No	
Insulation	Expanded	
Outside diameter	Diameter	8.1 mm
	Signs	±
	Tolerance	0.5
Outside diameter	8.1 mm ± 0.5	
Sheath material	Radox EM 104	
Sheathing colour	blue	
Shielded	Yes	

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-07	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-07	ECLASS 11.0	27-06-03-07
ECLASS 12.0	27-06-03-07	ECLASS 13.0	27-06-03-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

HDC XX6A01 MFSXXXX-4000

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

M12	1	White, Orange	1	M12
	2	Orange	2	
	3	White, Green	3	
	4	Green	4	
	5	White, Brown	5	
	6	Brown	6	
	7	White, Blue	7	
	8	Blue	8	