


**APGTB 1.5 FT 2C/1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Some applications demand for a pluggable, modular solution to be more flexible or to facilitate the installation. Where complete functional units have to be prefabricated or replaced, modular and flexible connection systems are required. Our pluggable terminal blocks can be quickly assembled and are completely factory tested.

**General ordering data**

|            |   |
|------------|---|
| Version    | Feed-through terminal, PUSH IN, 1.5 mm <sup>2</sup> , 500 V, 17.5 A, dark beige |
| Order No.  | <a href="#">2482160000</a>  |
| Type       | APGTB 1.5 FT 2C/1   |
| GTIN (EAN) | 4050118494228   |
| Qty.       | 50 pc(s).   |

## APGTB 1.5 FT 2C/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 33.5 mm    | Depth (inches) | 1.319 inch |
| Depth including DIN rail | 34.5 mm    | Height         | 55 mm      |
| Height (inches)          | 2.165 inch | Width          | 3.5 mm     |
| Width (inches)           | 0.138 inch | Net weight     | 3.9 g      |

## Temperatures

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C         |                                  |        |

## Material data

|                                |        |                           |            |
|--------------------------------|--------|---------------------------|------------|
| Material                       | Wemid  | Colour                    | dark beige |
| Colour of operational elements | orange | UL 94 flammability rating | V-0        |

## Rating data IECEx/ATEX

|                                |                     |                                 |                     |
|--------------------------------|---------------------|---------------------------------|---------------------|
| Certificate No. (ATEX)         | TUEV16ATEX7940U     | Certificate No. (IECEX)         | IECEXTUR16.0046U    |
| Max. voltage (ATEX)            | 500 V               | Current (ATEX)                  | 10.5 A              |
| Wire cross section max. (ATEX) | 1.5 mm <sup>2</sup> | Max. voltage (IECEX)            | 500 V               |
| Current (IECEX)                | 10.5 A              | Wire cross section max. (IECEX) | 1.5 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex ec II C Gc       | Ex 2014/34/EU label             | II 3 G D            |

## System specifications

|                               |     |                                     |       |
|-------------------------------|-----|-------------------------------------|-------|
| End cover plate required      | Yes | Number of potentials                | 1     |
| Number of levels              | 1   | Number of clamping points per level | 2     |
| Number of potentials per tier | 1   | Levels cross-connected internally   | No    |
| PE connection                 | No  | Rail                                | TS 35 |
| N-function                    | No  | PE function                         | No    |
| PEN function                  | No  |                                     |       |

## Additional technical data

|                          |         |                     |       |
|--------------------------|---------|---------------------|-------|
| Explosion-tested version | No      | Installation advice | Rail  |
| Open sides               | right   | Snap-on             | No    |
| Type of fixing           | Snap-on | Type of mounting    | TS 35 |
| With snap-in pegs        | No      |                     |       |

## CSA rating data

|                               |                 |                               |        |
|-------------------------------|-----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-70089609 | Current size B (CSA)          | 13 A   |
| Current size C (CSA)          | 13 A            | Current size D (CSA)          | 5 A    |
| Voltage size B (CSA)          | 300 V           | Voltage size C (CSA)          | 300 V  |
| Voltage size D (CSA)          | 600 V           | Wire cross section max. (CSA) | 14 AWG |
| Wire cross section min. (CSA) | 26 AWG          |                               |        |

## APGTB 1.5 FT 2C/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|   |                      |   |                     |
|---|----------------------|---|---------------------|
| Blade size  | 0.4 x 2.0 mm         | Clamping range, max.  | 1.5 mm <sup>2</sup> |
| Clamping range, min.  | 0.14 mm <sup>2</sup> | Connection cross-section, stranded, max.  | 1.5 mm <sup>2</sup> |
| Connection cross-section, stranded, min.  | 0.5 mm <sup>2</sup>  | Connection direction  | top                 |
| Gauge to IEC 60947-1  | A1                   | Number of connections   | 2                   |
| Stripping length  | 8 mm                 | Type of connection  | PUSH IN             |
| Type of connection 2  | Plug-in connection   | Wire connection cross section AWG, max.   | AWG 14              |
| Wire connection cross section AWG, min.   | AWG 26               | Wire connection cross section, finely stranded, max.                                    | 1.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, solid core, max.   | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, min.   | 0.5 mm <sup>2</sup>  |   |                     |

## General

|   |                                  |   |        |
|---|----------------------------------|---|--------|
| Installation advice                     | Rail                             | Rail                                    | TS 35  |
| Standards                               | In accordance with IEC 60947-7-1 | Wire connection cross section AWG, max. | AWG 14 |
| Wire connection cross section AWG, min. | AWG 26                           |   |        |

## PE rating data

|              |    |
|--------------|----|
| PEN function | No |
|--------------|----|

## Rating data

|  |                     |                                 |                                  |
|--|---------------------|---------------------------------|----------------------------------|
| Rated cross-section                          | 1.5 mm <sup>2</sup> | Rated voltage                   | 500 V                            |
| Rated DC voltage                             | 500 V               | Rated current                   | 17.5 A                           |
| Current at maximum wires                     | 17.5 A              | Standards                       | In accordance with IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.83 mΩ             | Rated impulse withstand voltage | 6 kV                             |
| Power loss in accordance with IEC 60947-7-x  | 0.56 W              | Pollution severity              | 3                                |
| Surge voltage category                       | III                 |                                 |                                  |

## UL rating data

|  |        |  |        |
|--|--------|--|--------|
| Certificate No. (cURus)                    | E60693 | Conductor size Factory wiring max. (cURus) | 14 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus)   | 14 AWG |
| Conductor size Field wiring min. (cURus)   | 26 AWG | Current size B (cURus)                     | 13 A   |
| Current size C (cURus)                     | 13 A   | Current size D (cURus)                     | 5 A    |
| Voltage size B (cURus)                     | 300 V  | Voltage size C (cURus)                     | 300 V  |
| Voltage size D (cURus)                     | 600 V  |  |        |

## APGTB 1.5 FT 2C/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 7.0    | EC000897    | ETIM 8.0    | EC000897    |
| ETIM 9.0    | EC000897    | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-17 |

## Environmental Product Compliance

REACH SVHC

/

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E60693     |

## Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">ATEX Certificate</a><br><a href="#">Attestation of Conformity</a><br><a href="#">NTI APGTB 1.5 FT 2C/1</a><br><a href="#">IECEX Certificate</a><br><a href="#">DNVGL certificate</a><br><a href="#">CCC Ex Certificate</a><br><a href="#">CE Declaration of Conformity</a><br><a href="#">UKCA declaration of conformity</a><br><a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Tender specification                        | <a href="#">Klippon® Connect 2482160000 DE</a><br><a href="#">Klippon® Connect 2482160000 EN</a>   |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a><br><a href="#">User Manual APGTB FT</a>  |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |

### APGTB 1.5 FT 2C/1

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

