

**AEP 3C 10/16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | A-series, End plate        |
| Order No.  | <a href="#">2490530000</a> |
| Type       | AEP 3C 10/16               |
| GTIN (EAN) | 4050118500912              |
| Qty.       | 20 pc(s).                  |

**AEP 3C 10/16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |           |                 |            |
|------------|-----------|-----------------|------------|
| Depth      | 44.4 mm   | Depth (inches)  | 1.748 inch |
| Height     | 100.23 mm | Height (inches) | 3.946 inch |
| Width      | 2.1 mm    | Width (inches)  | 0.083 inch |
| Net weight | 4.767 g   |                 |            |

**Temperatures**

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C         |                                  |        |

**Material data**

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ECLASS 9.1  | 27-14-11-33 | ECLASS 10.0 | 27-14-11-33 |
| ECLASS 11.0 | 27-14-11-33 | ECLASS 12.0 | 27-14-11-33 |
| ECLASS 13.0 | 27-25-03-01 |             |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                              |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>              |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                     |