


**SET AAP11 6/1.5/24C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The unique modular concept can be tailored to every type of machine. The potential distribution terminal blocks AAP are successful thanks to their uniform design with two possible constructions – alternating or grouped. In the grouped structure of the control voltage distribution, the potentials are located on different terminal blocks and thus form entire potential blocks.

**General ordering data**

|            |  |
|------------|--|
| Version    | Modular distribution terminals, PUSH IN, 6 mm <sup>2</sup> , 500 V, 41 A, dark beige |
| Order No.  | <a href="#">2506370000</a>   |
| Type       | SET AAP11 6/1.5/24C  |
| GTIN (EAN) | 4050118520750  |
| Qty.       | 1 pc(s).   |



## SET AAP11 6/1.5/24C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                |           |
|--------------------------|------------|----------------|-----------|
| Depth                    | 47 mm      | Depth (inches) | 1.85 inch |
| Depth including DIN rail | 48 mm      | Height         | 85.5 mm   |
| Height (inches)          | 3.366 inch | Width          | 49 mm     |
| Width (inches)           | 1.929 inch | Net weight     | 107.855 g |

## Temperatures

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C         |                                  |        |

## Material data

|                                |       |                           |            |
|--------------------------------|-------|---------------------------|------------|
| Material                       | Wemid | Colour                    | dark beige |
| Colour of operational elements | red   | UL 94 flammability rating | V-0        |

## Rating data IECEx/ATEX

|                    |               |                     |          |
|--------------------|---------------|---------------------|----------|
| Marking EN 60079-7 | Ex ec II C Gc | Ex 2014/34/EU label | II 2 G D |
|--------------------|---------------|---------------------|----------|

## System specifications

|                               |    |                                     |       |
|-------------------------------|----|-------------------------------------|-------|
| End cover plate required      | No | Number of potentials                | 2     |
| Number of levels              | 1  | Number of clamping points per level | 50    |
| Number of potentials per tier | 2  | Levels cross-connected internally   | No    |
| PE connection                 | No | Rail                                | TS 35 |
| N-function                    | No | PE function                         | No    |
| PEN function                  | No |                                     |       |

## Additional technical data

|                          |       |                     |         |
|--------------------------|-------|---------------------|---------|
| Explosion-tested version | Yes   | Installation advice | Rail    |
| Open sides               | right | Type of fixing      | Snap-on |
| Type of mounting         | TS 35 |                     |         |

## Conductors for clamping (additional connection)

|   |                      |   |                     |
|---|----------------------|---|---------------------|
| Blade size, additional connection   | 0.4 x 2.0 mm         | Clamping range, further connection, max.  | 1.5 mm <sup>2</sup> |
| Clamping range, further connection, min.  | 0.14 mm <sup>2</sup> | Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max. | 1 mm <sup>2</sup>   |
| Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, min. | 0.5 mm <sup>2</sup>  | Conductor cross-section, flexible, further connection, min.                                 | 0.5 mm <sup>2</sup> |
| Connection direction  | top                  | Connection type, additional connection  | PUSH IN             |
| Cross-section for connected wire, AWG, additional connection, max.                          | AWG 14               | Cross-section for connected wire, AWG, additional connection, min.                          | AWG 26              |
| Cross-section for connected wire, flexible, further connection, max.                        | 1.5 mm <sup>2</sup>  | Cross-section for connected wire, multi-core, further connection, max.                      | 1.5 mm <sup>2</sup> |
| Cross-section for connected wire, multi-core, further connection, min.                      | 0.5 mm <sup>2</sup>  | Cross-section for connected wire, solid-core, further connection, max.                      | 1.5 mm <sup>2</sup> |
| Cross-section for connected wire, solid-core, further connection, min.                      | 0.5 mm <sup>2</sup>  | Rated cross-section, further connection   | 1.5 mm <sup>2</sup> |
| Stripping length, additional connection   | 8 mm                 |   |                     |



## SET AAP11 6/1.5/24C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|   |  |         |                      |
|---|--|---------|----------------------|
| Blade size  | 1.0 x 5.5 mm                           |         |                      |
| Clamping range, max.  | 6 mm <sup>2</sup>                      |         |                      |
| Clamping range, min.  | 0.34 mm <sup>2</sup>                   |         |                      |
| Connection cross-section, stranded, max.                            | 6 mm <sup>2</sup>                      |         |                      |
| Connection cross-section, stranded, min.                            | 0.5 mm <sup>2</sup>                    |         |                      |
| Connection direction  | top                                    |         |                      |
| Gauge to IEC 60947-1  | A5                                     |         |                      |
| Number of connections   | 1                                      |         |                      |
| Stripping length  | 12 mm                                  |         |                      |
| Tube length for twin wire-end ferrule                               | Tube length                            | max.    | 12 mm                |
|   |  | min.    | 10 mm                |
|   | Cross-section for conductor connection | nominal | 0.5 mm <sup>2</sup>  |
|   | Tube length                            | max.    | 18 mm                |
|   |  | min.    | 10 mm                |
|   | Cross-section for conductor connection | nominal | 0.75 mm <sup>2</sup> |
|   | Tube length                            | max.    | 18 mm                |
|   |  | min.    | 12 mm                |
|   | Cross-section for conductor connection | min.    | 1 mm <sup>2</sup>    |
|   |  | max.    | 1.5 mm <sup>2</sup>  |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4    | Tube length                            | max.    | 12 mm                |
|   |  | min.    | 10 mm                |
|   | Cross-section for conductor connection | min.    | 0.5 mm <sup>2</sup>  |
|   |  | max.    | 1 mm <sup>2</sup>    |
|   | Tube length                            | max.    | 18 mm                |
|   |  | min.    | 10 mm                |
|   | Cross-section for conductor connection | nominal | 1.5 mm <sup>2</sup>  |
|   | Tube length                            | max.    | 18 mm                |
|   |  | min.    | 12 mm                |
|   | Cross-section for conductor connection | nominal | 2.5 mm <sup>2</sup>  |
|   | Tube length                            | max.    | 18 mm                |
|   |  | min.    | 10 mm                |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Cross-section for conductor connection | min.    | 0.5 mm <sup>2</sup>  |
|   |  | max.    | 1 mm <sup>2</sup>    |
|   | Tube length                            | min.    | 10 mm                |
|   |  | max.    | 18 mm                |
|   | Cross-section for conductor connection | min.    | 1.5 mm <sup>2</sup>  |
|   |  | max.    | 2.5 mm <sup>2</sup>  |
|   |  | min.    | 12 mm                |
|   | Cross-section for conductor connection | nominal | 4 mm <sup>2</sup>    |
|   | Tube length                            | max.    | 18 mm                |
|   |  | min.    | 10 mm                |
|   | Cross-section for conductor connection | min.    | 6 mm <sup>2</sup>    |
|   |  | max.    | 10 mm <sup>2</sup>   |
| Twin wire-end ferrules, max.  | 1.5 mm <sup>2</sup>                    |         |                      |
| Twin wire-end ferrules, min.  | 0.5 mm <sup>2</sup>                    |         |                      |
| Type of connection  | PUSH IN                                |         |                      |
| Wire connection cross section AWG, max.                             | AWG 8                                  |         |                      |
| Wire connection cross section AWG, min.                             | AWG 22                                 |         |                      |



## SET AAP11 6/1.5/24C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|   |                     |
|---|---------------------|
| Wire connection cross section, finely stranded, max.                                    | 6 mm <sup>2</sup>   |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.   | 6 mm <sup>2</sup>   |
| Wire connection cross-section, solid core, min.   | 0.5 mm <sup>2</sup> |

## General

|   |                                  |   |       |
|---|----------------------------------|---|-------|
| Installation advice                     | Rail                             | Rail                                    | TS 35 |
| Standards                               | In accordance with IEC 60947-7-1 | Wire connection cross section AWG, max. | AWG 8 |
| Wire connection cross section AWG, min. | AWG 22                           |   |       |

## Rating data

|  |                   |                                 |                                  |
|--|-------------------|---------------------------------|----------------------------------|
| Rated cross-section                          | 6 mm <sup>2</sup> | Rated voltage                   | 500 V                            |
| Rated DC voltage                             | 500 V             | Rated current                   | 41 A                             |
| Current at maximum wires                     | 41 A              | Standards                       | In accordance with IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 0.78 mΩ           | Rated impulse withstand voltage | 6 kV                             |
| Power loss in accordance with IEC 60947-7-x  | 1.31 W            | Pollution severity              | 3                                |
| Surge voltage category                       | III               |                                 |                                  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001284    | ETIM 7.0    | EC001284    |
| ETIM 8.0    | EC001284    | ETIM 9.0    | EC001284    |
| ECLASS 9.0  | 27-14-11-06 | ECLASS 9.1  | 27-14-11-06 |
| ECLASS 10.0 | 27-14-11-06 | ECLASS 11.0 | 27-14-11-06 |
| ECLASS 12.0 | 27-14-11-06 | ECLASS 13.0 | 27-14-11-06 |

## Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

## Approvals

|           |
|-----------|
| Approvals |
|-----------|



Creation date July 5, 2024 3:27:06 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.



## SET AAP11 6/1.5/24C

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">DE PT0205 20180316 014 ISSUE01.pdf</a><br><a href="#">DNVGL certificate</a><br><a href="#">UKCA declaration of conformity</a><br><a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>   |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a><br><a href="#">User Manual AXC 1.5-16</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>  |



## SET AAP11 6/1.5/24C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DEK 5/8



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | DEK 5/8 MM WS              | Version  |
| Order No.  | <a href="#">2007130000</a> | Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392012              |  |
| Qty.       | 500 pc(s).                 |  |

## Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SDS 0.4X2.0X60             | Version  |
| Order No.  | <a href="#">2749260000</a> | Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm |
| GTIN (EAN) | 4050118895537              |  |
| Qty.       | 1 pc(s).                   |  |



**SET AAP11 6/1.5/24C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****A-Series**

# A Series

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

**General ordering data**

|            |                            |                       |
|------------|----------------------------|-----------------------|
| Type       | AEB 35 SCL/1 V0 GY         | Version               |
| Order No.  | <a href="#">2661290000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702170              |                       |
| Qty.       | 20 pc(s).                  |                       |
| Type       | AEB 35 SCL/1 V0            | Version               |
| Order No.  | <a href="#">2661280000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702163              |                       |
| Qty.       | 20 pc(s).                  |                       |
| Type       | AEB 35 SCL/1 V0 BK         | Version               |
| Order No.  | <a href="#">2661300000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702187              |                       |
| Qty.       | 20 pc(s).                  |                       |
| Type       | AEB 35 SC/1                | Version               |
| Order No.  | <a href="#">1991920000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118376722              |                       |
| Qty.       | 50 pc(s).                  |                       |
| Type       | AEB 35 SC/1 BK             | Version               |
| Order No.  | <a href="#">2475310000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118487114              |                       |
| Qty.       | 50 pc(s).                  |                       |

**A-Series**

# A Series

Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | AAM 6 YE FLASH             | Version  |
| Order No.  | <a href="#">2635570000</a> | Terminal marker, 13 x 8.1 mm, Pitch in mm (P): 8.00 yellow |
| GTIN (EAN) | 4050118674514              |  |
| Qty.       | 40 pc(s).                  |  |



**SET AAP11 6/1.5/24C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Custom printing**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/8 MC SDR             | Version   |
| Order No.  | <a href="#">1856750000</a> | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248400867              | Weidmueller, To customer specification                    |
| Qty.       | 160 pc(s).                 |   |
| Type       | DEK 5/8 PLUS MC SDR        | Version   |
| Order No.  | <a href="#">1046370000</a> | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248782079              | Weidmueller, To customer specification                    |
| Qty.       | 160 pc(s).                 |   |



## SET AAP11 6/1.5/24C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

| Type       | WS 10/8 PLUS MC NE WS      | Version  |
|------------|----------------------------|--|
| Order No.  | <a href="#">1905950000</a> | WS, Terminal marker, 10 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, |
| GTIN (EAN) | 4032248528103              | white  |
| Qty.       | 420 pc(s).                 |  |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

| Type       | DEK 5/8 MC NE WS           | Version   |
|------------|----------------------------|---|
| Order No.  | <a href="#">1856740000</a> | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248400850              | Weidmueller, white  |
| Qty.       | 800 pc(s).                 |   |



## SET AAP11 6/1.5/24C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 pc(s).                 |                            |
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 pc(s).                 |                            |

1.5 mm<sup>2</sup>

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | ZQV 1.5N/7 RD              | Version  |
| Order No.  | <a href="#">1985750000</a> | Cross-connector (terminal), Plugged, Number of poles: 7, Pitch in mm |
| GTIN (EAN) | 4050118370249              | (P): 3.50, Insulated: Yes, 17.5 A, red                               |
| Qty.       | 20 pc(s).                  |  |
| Type       | ZQV 1.5N/4 RD              | Version  |
| Order No.  | <a href="#">1985690000</a> | Cross-connector (terminal), Plugged, Number of poles: 4, Pitch in mm |
| GTIN (EAN) | 4050118370515              | (P): 3.50, Insulated: Yes, 17.5 A, red                               |
| Qty.       | 60 pc(s).                  |  |
| Type       | ZQV 1.5N/9 RD              | Version  |
| Order No.  | <a href="#">1985790000</a> | Cross-connector (terminal), Plugged, Number of poles: 9, Pitch in mm |
| GTIN (EAN) | 4050118370386              | (P): 3.50, Insulated: Yes, 17.5 A, red                               |
| Qty.       | 20 pc(s).                  |  |
| Type       | ZQV 1.5N/8 RD              | Version  |
| Order No.  | <a href="#">1985770000</a> | Cross-connector (terminal), Plugged, Number of poles: 8, Pitch in mm |
| GTIN (EAN) | 4050118370508              | (P): 3.50, Insulated: Yes, 17.5 A, red                               |
| Qty.       | 20 pc(s).                  |  |



## SET AAP11 6/1.5/24C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZQV 1.5N/20 RD             | Version   |
| Order No.  | <a href="#">1985810000</a> | Cross-connector (terminal), Plugged, Number of poles: 20, Pitch in mm |
| GTIN (EAN) | 4050118370355              | (P): 3.50, Insulated: Yes, 17.5 A, red                                |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 1.5N/2 RD              | Version   |
| Order No.  | <a href="#">1985650000</a> | Cross-connector (terminal), Plugged, Number of poles: 2, Pitch in mm  |
| GTIN (EAN) | 4050118370324              | (P): 3.50, Insulated: Yes, 17.5 A, red                                |
| Qty.       | 60 pc(s).                  |   |
| Type       | ZQV 1.5N/5 RD              | Version   |
| Order No.  | <a href="#">1985710000</a> | Cross-connector (terminal), Plugged, Number of poles: 5, Pitch in mm  |
| GTIN (EAN) | 4050118370256              | (P): 3.50, Insulated: Yes, 17.5 A, red                                |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 1.5N/6 RD              | Version   |
| Order No.  | <a href="#">1985730000</a> | Cross-connector (terminal), Plugged, Number of poles: 6, Pitch in mm  |
| GTIN (EAN) | 4050118370454              | (P): 3.50, Insulated: Yes, 17.5 A, red                                |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 1.5N/3 RD              | Version   |
| Order No.  | <a href="#">1985670000</a> | Cross-connector (terminal), Plugged, Number of poles: 3, Pitch in mm  |
| GTIN (EAN) | 4050118370348              | (P): 3.50, Insulated: Yes, 17.5 A, red                                |
| Qty.       | 60 pc(s).                  |   |
| Type       | ZQV 1.5N/50 RD             | Version   |
| Order No.  | <a href="#">1985820000</a> | Cross-connector (terminal), Plugged, Number of poles: 50, Pitch in mm |
| GTIN (EAN) | 4050118370270              | (P): 3.50, Insulated: Yes, 17.5 A, red                                |
| Qty.       | 5 pc(s).                   |   |
| Type       | ZQV 1.5N/10 RD             | Version   |
| Order No.  | <a href="#">1985800000</a> | Cross-connector (terminal), Plugged, Number of poles: 10, Pitch in mm |
| GTIN (EAN) | 4050118370393              | (P): 3.50, Insulated: Yes, 17.5 A, red                                |
| Qty.       | 20 pc(s).                  |   |

## Digital current clamp devices



Digital current clamp devices and attachments and adapters are used for measuring AC and DC currents. The significant advantage of these devices is that you can make a measurement without breaking the flow of current.

## General ordering data

|            |                            |            |
|------------|----------------------------|------------|
| Type       | ZUB MULTIMETER             | Version    |
| Order No.  | <a href="#">9205270000</a> | Multimeter |
| GTIN (EAN) | 4032248723522              |            |
| Qty.       | 1 pc(s).                   |            |



## SET AAP11 6/1.5/24C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | WS 10/8 PLUS MC SDR        | Version  |
| Order No.  | <a href="#">1906030000</a> | WS, Terminal marker, 10 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, |
| GTIN (EAN) | 4032248528196              | To customer specification  |
| Qty.       | 84 pc(s).                  |  |