


APGTB 1.5 2T 4C/2 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Some applications demand for a pluggable, modular solution to be more flexible or to facilitate the installation. Where complete functional units have to be prefabricated or replaced, modular and flexible connection systems are required. Our pluggable terminal blocks can be quickly assembled and are completely factory tested.

General ordering data

| | |
|------------|---|
| Version | Feed-through terminal, PUSH IN, 1.5 mm ² , 500 V, 17.5 A, blue |
| Order No. | 2485850000 |
| Type | APGTB 1.5 2T 4C/2 BL |
| GTIN (EAN) | 4050118496093 |
| Qty. | 50 pc(s). |

APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------------------------|------------|----------------|------------|
| Depth | 45 mm | Depth (inches) | 1.772 inch |
| Depth including DIN rail | 46 mm | Height | 84.5 mm |
| Height (inches) | 3.327 inch | Width | 3.5 mm |
| Width (inches) | 0.138 inch | Net weight | 7.618 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Material data

| | | | |
|--------------------------------|--------|---------------------------|------|
| Material | Wemid | Colour | blue |
| Colour of operational elements | orange | UL 94 flammability rating | V-0 |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|---------------------|---------------------------------|---------------------|
| Certificate No. (ATEX) | TUEV16ATEX7940U | Certificate No. (IECEX) | IECEXTUR16.0046U |
| Max. voltage (ATEX) | 500 V | Current (ATEX) | 10.5 A |
| Wire cross section max. (ATEX) | 1.5 mm ² | Max. voltage (IECEX) | 500 V |
| Current (IECEX) | 10.5 A | Wire cross section max. (IECEX) | 1.5 mm ² |
| Marking EN 60079-7 | Ex ec II C Gc | Ex 2014/34/EU label | II 3 G D |

System specifications

| | | | |
|-------------------------------|-----|-------------------------------------|-------|
| End cover plate required | Yes | Number of potentials | 2 |
| Number of levels | 2 | Number of clamping points per level | 2 |
| Number of potentials per tier | 1 | Levels cross-connected internally | No |
| PE connection | No | Rail | TS 35 |
| N-function | No | PE function | No |
| PEN function | No | | |

Additional technical data

| | | | |
|---------------------|-------|-------------------|---------|
| Installation advice | Rail | Open sides | right |
| Snap-on | No | Type of fixing | Snap-on |
| Type of mounting | TS 35 | With snap-in pegs | No |

CSA rating data

| | | | |
|-------------------------------|-----------------|-------------------------------|--------|
| Certificate No. (CSA) | 200039-70089609 | Current size B (CSA) | 13 A |
| Current size C (CSA) | 13 A | Current size D (CSA) | 5 A |
| Voltage size B (CSA) | 300 V | Voltage size C (CSA) | 300 V |
| Voltage size D (CSA) | 600 V | Wire cross section max. (CSA) | 14 AWG |
| Wire cross section min. (CSA) | 26 AWG | | |

APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Conductors for clamping (rated connection)

| | | | |
|---|----------------------|---|---------------------|
| Blade size | 0.4 x 2.0 mm | Clamping range, max. | 1.5 mm ² |
| Clamping range, min. | 0.14 mm ² | Connection cross-section, stranded, max. | 1.5 mm ² |
| Connection cross-section, stranded, min. | 0.5 mm ² | Connection direction | top |
| Gauge to IEC 60947-1 | A1 | Number of connections | 4 |
| Stripping length | 8 mm | Type of connection | PUSH IN |
| Type of connection 2 | Plug-in connection | Wire connection cross section AWG, max. | AWG 14 |
| Wire connection cross section AWG, min. | AWG 26 | Wire connection cross section, finely stranded, max. | 1.5 mm ² |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 1.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, solid core, max. | 1.5 mm ² |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | | |

General

| | | | |
|---|----------------------------------|---|--------|
| Installation advice | Rail | Rail | TS 35 |
| Standards | In accordance with IEC 60947-7-1 | Wire connection cross section AWG, max. | AWG 14 |
| Wire connection cross section AWG, min. | AWG 26 | | |

PE rating data

| | |
|--------------|----|
| PEN function | No |
|--------------|----|

Rating data

| | | | |
|--|---------------------|---------------------------------|----------------------------------|
| Rated cross-section | 1.5 mm ² | Rated voltage | 500 V |
| Rated DC voltage | 500 V | Rated current | 17.5 A |
| Current at maximum wires | 17.5 A | Standards | In accordance with IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.83 mΩ | Rated impulse withstand voltage | 6 kV |
| Power loss in accordance with IEC 60947-7-x | 0.56 W | Pollution severity | 3 |
| Surge voltage category | III | | |

UL rating data

| | | | |
|--|--------|--|--------|
| Certificate No. (cURus) | E60693 | Conductor size Factory wiring max. (cURus) | 14 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus) | 14 AWG |
| Conductor size Field wiring min. (cURus) | 26 AWG | Current size B (cURus) | 13 A |
| Current size C (cURus) | 13 A | Current size D (cURus) | 5 A |
| Voltage size B (cURus) | 300 V | Voltage size C (cURus) | 300 V |
| Voltage size D (cURus) | 600 V | | |

APGTB 1.5 2T 4C/2 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Classifications**

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 7.0 | EC000897 | ETIM 8.0 | EC000897 |
| ETIM 9.0 | EC000897 | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-17 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E60693 |

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | ATEX Certificate Attestation of Conformity IECEX Certificate DNVGL certificate CCC Ex Certificate CE Declaration of Conformity UKCA declaration of conformity Confirmation of Standards EN 45545-2_2020-10 |
| Engineering Data | CAD data – STEP |
| Tender specification | Klippon® Connect 2485850000 DE Klippon® Connect 2485850000 EN |
| User Documentation | Usage of terminals in EXi atmospheres StorageConditionsTerminalBlocks NTI APTB 1.5 2T 4C/2 User Manual APTB FT |
| Catalogues | Catalogues in PDF-format |

APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

1.5 mm²


1.5
mm²

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | ZQV 1.5N/50 | Version |
| Order No. | 1985620000 | Cross-connector (terminal), Plugged, Number of poles: 50, Pitch in mm |
| GTIN (EAN) | 4050118370300 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 5 pc(s). | |
| Type | ZQV 1.5N/8 BL | Version |
| Order No. | 1985640000 | Cross-connector (terminal), Plugged, Number of poles: 8, Pitch in mm |
| GTIN (EAN) | 4050118370461 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/6 | Version |
| Order No. | 1985510000 | Cross-connector (terminal), Plugged, Number of poles: 6, Pitch in mm |
| GTIN (EAN) | 4050118370188 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/3 BL | Version |
| Order No. | 1985550000 | Cross-connector (terminal), Plugged, Number of poles: 3, Pitch in mm |
| GTIN (EAN) | 4050118370485 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/8 RD | Version |
| Order No. | 1985770000 | Cross-connector (terminal), Plugged, Number of poles: 8, Pitch in mm |
| GTIN (EAN) | 4050118370508 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/2 BL | Version |
| Order No. | 1985530000 | Cross-connector (terminal), Plugged, Number of poles: 2, Pitch in mm |
| GTIN (EAN) | 4050118370423 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/2 RD | Version |
| Order No. | 1985650000 | Cross-connector (terminal), Plugged, Number of poles: 2, Pitch in mm |
| GTIN (EAN) | 4050118370324 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/4 BL | Version |
| Order No. | 1985570000 | Cross-connector (terminal), Plugged, Number of poles: 4, Pitch in mm |
| GTIN (EAN) | 4050118370317 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/6 BL | Version |
| Order No. | 1985610000 | Cross-connector (terminal), Plugged, Number of poles: 6, Pitch in mm |
| GTIN (EAN) | 4050118370492 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/10 | Version |
| Order No. | 1985580000 | Cross-connector (terminal), Plugged, Number of poles: 10, Pitch in mm |
| GTIN (EAN) | 4050118370416 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 20 pc(s). | |

Creation date May 23, 2024 6:57:17 AM CEST

APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | ZQV 1.5N/3 RD | Version |
| Order No. | 1985670000 | Cross-connector (terminal), Plugged, Number of poles: 3, Pitch in mm |
| GTIN (EAN) | 4050118370348 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/4 RD | Version |
| Order No. | 1985690000 | Cross-connector (terminal), Plugged, Number of poles: 4, Pitch in mm |
| GTIN (EAN) | 4050118370515 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/2 | Version |
| Order No. | 1985410000 | Cross-connector (terminal), Plugged, Number of poles: 2, Pitch in mm |
| GTIN (EAN) | 4050118369861 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/4 | Version |
| Order No. | 1985490000 | Cross-connector (terminal), Plugged, Number of poles: 4, Pitch in mm |
| GTIN (EAN) | 4050118370201 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/7 RD | Version |
| Order No. | 1985750000 | Cross-connector (terminal), Plugged, Number of poles: 7, Pitch in mm |
| GTIN (EAN) | 4050118370249 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/3 | Version |
| Order No. | 1985480000 | Cross-connector (terminal), Plugged, Number of poles: 3, Pitch in mm |
| GTIN (EAN) | 4050118370096 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 60 pc(s). | |
| Type | ZQV 1.5N/20 | Version |
| Order No. | 1985600000 | Cross-connector (terminal), Plugged, Number of poles: 20, Pitch in mm |
| GTIN (EAN) | 4050118370225 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/50 BL | Version |
| Order No. | 1985720000 | Cross-connector (terminal), Plugged, Number of poles: 50, Pitch in mm |
| GTIN (EAN) | 4050118370546 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 5 pc(s). | |
| Type | ZQV 1.5N/8 | Version |
| Order No. | 1985540000 | Cross-connector (terminal), Plugged, Number of poles: 8, Pitch in mm |
| GTIN (EAN) | 4050118370218 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/6 RD | Version |
| Order No. | 1985730000 | Cross-connector (terminal), Plugged, Number of poles: 6, Pitch in mm |
| GTIN (EAN) | 4050118370454 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/10 BL | Version |
| Order No. | 1985680000 | Cross-connector (terminal), Plugged, Number of poles: 10, Pitch in mm |
| GTIN (EAN) | 4050118370539 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/7 | Version |
| Order No. | 1985520000 | Cross-connector (terminal), Plugged, Number of poles: 7, Pitch in mm |
| GTIN (EAN) | 4050118370195 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/20 BL | Version |
| Order No. | 1985700000 | Cross-connector (terminal), Plugged, Number of poles: 20, Pitch in mm |
| GTIN (EAN) | 4050118370331 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 20 pc(s). | |

Creation date May 23, 2024 6:57:17 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | ZQV 1.5N/5 | Version |
| Order No. | 1985500000 | Cross-connector (terminal), Plugged, Number of poles: 5, Pitch in mm |
| GTIN (EAN) | 4050118369991 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/9 RD | Version |
| Order No. | 1985790000 | Cross-connector (terminal), Plugged, Number of poles: 9, Pitch in mm |
| GTIN (EAN) | 4050118370386 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/9 | Version |
| Order No. | 1985560000 | Cross-connector (terminal), Plugged, Number of poles: 9, Pitch in mm |
| GTIN (EAN) | 4050118370409 | (P): 3.50, Insulated: Yes, 17.5 A, orange |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/10 RD | Version |
| Order No. | 1985800000 | Cross-connector (terminal), Plugged, Number of poles: 10, Pitch in mm |
| GTIN (EAN) | 4050118370393 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/5 RD | Version |
| Order No. | 1985710000 | Cross-connector (terminal), Plugged, Number of poles: 5, Pitch in mm |
| GTIN (EAN) | 4050118370256 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/5 BL | Version |
| Order No. | 1985590000 | Cross-connector (terminal), Plugged, Number of poles: 5, Pitch in mm |
| GTIN (EAN) | 4050118370430 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/50 RD | Version |
| Order No. | 1985820000 | Cross-connector (terminal), Plugged, Number of poles: 50, Pitch in mm |
| GTIN (EAN) | 4050118370270 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 5 pc(s). | |
| Type | ZQV 1.5N/7 BL | Version |
| Order No. | 1985630000 | Cross-connector (terminal), Plugged, Number of poles: 7, Pitch in mm |
| GTIN (EAN) | 4050118370522 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/20 RD | Version |
| Order No. | 1985810000 | Cross-connector (terminal), Plugged, Number of poles: 20, Pitch in mm |
| GTIN (EAN) | 4050118370355 | (P): 3.50, Insulated: Yes, 17.5 A, red |
| Qty. | 20 pc(s). | |
| Type | ZQV 1.5N/9 BL | Version |
| Order No. | 1985660000 | Cross-connector (terminal), Plugged, Number of poles: 9, Pitch in mm |
| GTIN (EAN) | 4050118370478 | (P): 3.50, Insulated: Yes, 17.5 A, blue |
| Qty. | 20 pc(s). | |

APGTB 1.5 2T 4C/2 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****A-Series**A
Series

A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

General ordering data

| | | |
|------------|----------------------------|---------------------------|
| Type | APP 4 | Version |
| Order No. | 2489110000 | A-series, Partition plate |
| GTIN (EAN) | 4050118499322 | |
| Qty. | 50 pc(s). | |

Strain reliefs

The strain relief protects the contact against mechanical stress and protects the connector against inadvertent release from the contact point.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | APGSR 1.5 | Version |
| Order No. | 2482730000 | Strain relief (terminal), Wemid, orange |
| GTIN (EAN) | 4050118493993 | |
| Qty. | 25 pc(s). | |
| Type | APGSR 1.5 - 4P | Version |
| Order No. | 2482740000 | Strain relief (terminal), Wemid, orange |
| GTIN (EAN) | 4050118494204 | |
| Qty. | 25 pc(s). | |
| Type | APGSR 1.5 - 8P | Version |
| Order No. | 2482750000 | Strain relief (terminal), Wemid, orange |
| GTIN (EAN) | 4050118494211 | |
| Qty. | 25 pc(s). | |

APGTB 1.5 2T 4C/2 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Locking elements**

The plugs can be securely and easily fixed to the base terminal by using a locking element. The locking element avoids an unintentional disconnection of the plugs from the base terminal and ensures maximum safety.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | APGLE 1.5 | Version |
| Order No. | 2482720000 | Locking clips (terminal), Wemid, orange |
| GTIN (EAN) | 4050118496253 | |
| Qty. | 25 pc(s). | |

Protective covers

The cover of the plug contact offers protection from external influences, e.g. soiling from dust.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | APGPC 1.5 | Version |
| Order No. | 2482530000 | Terminal cover, Wemid, orange, Height: 16 mm, Width: 3.3 mm, |
| GTIN (EAN) | 4050118494563 | Depth: 13 mm |
| Qty. | 50 pc(s). | |

APGTB 1.5 2T 4C/2 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com**Accessories****SnapMark**

SnapMark - this tag carrier has been developed specifically for the I-series double-level terminal IDK 1.5N. The flexible pivot mechanism allows cross-connections to be easily installed or removed. It can hold four DEK 5 labelling tags or two WS 10/5 Middle connector markers.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SNAPMARK 1.5 | Version |
| Order No. | 2682080000 | Group markers, Terminal marker, 26 x 3.5 mm, Pitch in mm (P): 3.50 |
| GTIN (EAN) | 4050118821772 | Weidmueller, white |
| Qty. | 40 pc(s). | |

Slotted screwdriver

Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SDS 0.4X2.0X60 | Version |
| Order No. | 2749260000 | Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm |
| GTIN (EAN) | 4050118895537 | |
| Qty. | 1 pc(s). | |

APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

1.5 mm²


The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | APG 1.5 R GN | Version |
| Order No. | 2482330000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, green |
| GTIN (EAN) | 4050118494396 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5/6 | Version |
| Order No. | 2482390000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 6, dark beige |
| GTIN (EAN) | 4050118494457 | |
| Qty. | 25 pc(s). | |
| Type | APG 1.5 MI GN | Version |
| Order No. | 2482300000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, green |
| GTIN (EAN) | 4050118494365 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5 L BL | Version |
| Order No. | 2482260000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, blue |
| GTIN (EAN) | 4050118494297 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5 L | Version |
| Order No. | 2482250000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, dark beige |
| GTIN (EAN) | 4050118494280 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5/8 | Version |
| Order No. | 2482410000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 8, dark beige |
| GTIN (EAN) | 4050118494471 | |
| Qty. | 20 pc(s). | |
| Type | APG 1.5 MI BL | Version |
| Order No. | 2482290000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, blue |
| GTIN (EAN) | 4050118494327 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5/2 | Version |
| Order No. | 2482350000 | Plug, 1.5 mm ² , 500 V, 17.5 A, dark beige |
| GTIN (EAN) | 4050118494419 | |
| Qty. | 25 pc(s). | |
| Type | APG 1.5 MI | Version |
| Order No. | 2482280000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, dark beige |
| GTIN (EAN) | 4050118494310 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5 R | Version |
| Order No. | 2482310000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, dark beige |
| GTIN (EAN) | 4050118494372 | |
| Qty. | 50 pc(s). | |

Creation date May 23, 2024 6:57:17 AM CEST

APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | APG 1.5/9 | Version |
| Order No. | 2482420000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 9, dark beige |
| GTIN (EAN) | 4050118494488 | |
| Qty. | 20 pc(s). | |
| Type | APG 1.5/3 | Version |
| Order No. | 2482360000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 3, dark beige |
| GTIN (EAN) | 4050118494426 | |
| Qty. | 25 pc(s). | |
| Type | APG 1.5/10 | Version |
| Order No. | 2482430000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 10, dark beige |
| GTIN (EAN) | 4050118494495 | |
| Qty. | 20 pc(s). | |
| Type | APG 1.5/5 | Version |
| Order No. | 2482380000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 5, dark beige |
| GTIN (EAN) | 4050118494440 | |
| Qty. | 25 pc(s). | |
| Type | APG 1.5/7 | Version |
| Order No. | 2482400000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 7, dark beige |
| GTIN (EAN) | 4050118494464 | |
| Qty. | 25 pc(s). | |
| Type | APG 1.5 L GN | Version |
| Order No. | 2482270000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 1, green |
| GTIN (EAN) | 4050118494303 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5 R BL | Version |
| Order No. | 2482320000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 1, blue |
| GTIN (EAN) | 4050118494389 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5/1 | Version |
| Order No. | 2482340000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 1, dark beige |
| GTIN (EAN) | 4050118494402 | |
| Qty. | 50 pc(s). | |
| Type | APG 1.5/4 | Version |
| Order No. | 2482370000 | Plug, 1.5 mm², 500 V, 17.5 A, Number of poles: 4, dark beige |
| GTIN (EAN) | 4050118494433 | |
| Qty. | 25 pc(s). | |

APGTB 1.5 2T 4C/2 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

A-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | |
|------------|----------------------------|-----------------------|
| Type | AEB 35 SCL/1 V0 BK | Version |
| Order No. | 2661300000 | A-series, End bracket |
| GTIN (EAN) | 4050118702187 | |
| Qty. | 20 pc(s). | |
| Type | AEB 35 SC/1 | Version |
| Order No. | 1991920000 | A-series, End bracket |
| GTIN (EAN) | 4050118376722 | |
| Qty. | 50 pc(s). | |
| Type | AEB 35 SC/1 BK | Version |
| Order No. | 2475310000 | A-series, End bracket |
| GTIN (EAN) | 4050118487114 | |
| Qty. | 50 pc(s). | |
| Type | AEB 35 SCL/1 V0 | Version |
| Order No. | 2661280000 | A-series, End bracket |
| GTIN (EAN) | 4050118702163 | |
| Qty. | 20 pc(s). | |
| Type | AEB 35 SCL/1 V0 GY | Version |
| Order No. | 2661290000 | A-series, End bracket |
| GTIN (EAN) | 4050118702170 | |
| Qty. | 20 pc(s). | |

Coding elements



Through the use of coding pins, individual coding options ensure trouble-free plug-in connection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | APGCE | Version |
| Order No. | 1514490000 | Coding element (terminal), Wemid, orange, Width: 3.3 mm |
| GTIN (EAN) | 4050118321906 | |
| Qty. | 50 pc(s). | |