

UR67-MP-78-16DIO-12-60M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

**More performance. Simplified.
u-remote.**

Weidmüller u-remote – our innovative remote I/O concept with IP 67 which focuses purely on user benefits: tailored planning, faster installation, safer start-up, no more down-time. For considerably improved performance and greater productivity.

u-remote stands for "More Performance". Simplified

General ordering data

Version	Automation Products - u-remote IP67, Sensor-actuator active distributor, PROFINET V2.3, EtherNet/IP, EtherCAT, Multiprotocol
Order No.	2512830000
Type	UR67-MP-78-16DIO-12-60M
GTIN (EAN)	4050118527780
Qty.	1 pc(s).

UR67-MP-78-16DIO-12-60M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	17.3 mm	Height (inches)	0.681 inch
Width	59.6 mm	Width (inches)	2.346 inch
Length	206 mm	Length (inches)	8.11 inch
Net weight	500 g		

Connections

Fieldbus (BUS-IN)	1x M12 female 4-pole, D-coded	Fieldbus (BUS-OUT)	1x M12 female 4-pole, D-coded
I/O connections	8 x M12 socket 5-pole, A-coded	Supply voltage (AUX-IN)	1x 7/8" plug 5-pole
Supply voltage (AUX-OUT)	1x 7/8" socket 5-pole		

Digital inputs

Diagnostic display	Per channel, via LED, red	
Digital inputs	Short-circuit protection	Yes
	Overload protection	Yes
	Reverse polarity protection	Yes
Input current, high	Type 1 in acc. with IEC 61131-2	
Input current, low	Type 1 in acc. with IEC 61131-2	
Input type	Type 3 in acc. with IEC 61131-2	
Status indicator	Per channel, via LED, yellow	

Digital outputs

Diagnostic display	Per channel, via LED, red	
Digital outputs	Short-circuit protection	Yes
	Overload protection	Yes
	Reverse polarity protection	Yes
Max. total current outputs	9 A (12 A see manual)	
Output voltage, high	max. 2 V	
Output voltage, low	min. (UL -1)	
Short-circuit proof	Yes	
Status indicator	Per channel, via LED, yellow	
max. current-carrying capacity per output signal	2 A	

General data

Housing main material	Zinc diecast	Module variants	16 universal channels
Protection degree	IP67	UL 94 flammability rating	UL 94

Supply voltage

Limits	18 V DC ... 30 V DC	Operating voltage	24 V
Power consumption of module electronics	100 mA typical	Reverse polarity protection	Yes

UR67-MP-78-16DIO-12-60M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC001599	ETIM 7.0	EC001599
ETIM 8.0	EC001599	ETIM 9.0	EC001599
ECLASS 9.0	27-24-26-04	ECLASS 9.1	27-24-26-04
ECLASS 10.0	27-24-26-04	ECLASS 11.0	27-24-26-04
ECLASS 12.0	27-24-26-04	ECLASS 13.0	27-24-26-04

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	82327f13-cd27-455a-ab5b-a62e1996dcf8

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	CE Declaration of Conformity - DE UKCA Declaration of Conformity - EN
Engineering Data	CAD data – STEP
Software	Device description – UR67 - GSDML V2.33 / EDS V3.21 / ESI V1.2 files Device description – UR67 - GSDML V2.31 + V.33 / EDS V3.9 / ESI V1.2 files Device description – UR67 - IOLM 1.4
User Documentation	MAN UR67 MP DE MAN UR67 MP EN
Catalogues	Catalogues in PDF-format