

**IE-WL-BL-AP-CL-EU****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Features of the BasicLine (IE-WL-BL series)**

- IEEE 802.11a/b/g/n compliant access point / client
- MIMO technology for data rates up to 300 Mbit/s
- Fast roaming for interruption-free connection switching between access points
- DFS support in the 5 GHz band

**Features of the ValueLine (IE-WL-VL series)**

- IEEE 802.11a/b/g/n compliant access point / client / bridge
- MIMO technology for data rates up to 300 Mbit/s
- Fast roaming for interruption-free connection switching between access points
- DFS support in the 5 GHz band
- Power supply via PoE to IEEE 802.3af possible
- Integrated DI/DOs for monitoring and alarms

**General ordering data**

|            |   |
|------------|---|
| Version    | Wireless Access Point/Client, IEEE 802.11 a/b/g/n, EU-Model, IP30, 0 °C...60 °C |
| Order No.  | <a href="#">2536600000</a>  |
| Type       | IE-WL-BL-AP-CL-EU   |
| GTIN (EAN) | 4050118548655   |
| Qty.       | 1 pc(s).  |

## IE-WL-BL-AP-CL-EU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 70 mm  | Depth (inches)  | 2.756 inch |
| Height     | 115 mm | Height (inches) | 4.528 inch |
| Width      | 58 mm  | Width (inches)  | 2.283 inch |
| Net weight | 330 g  |                 |            |

## Temperatures

|                     |                            |                       |              |
|---------------------|----------------------------|-----------------------|--------------|
| Storage temperature | -40 °C...85 °C             | Operating temperature | 0 °C...60 °C |
| Humidity            | 5 to 95 % (non-condensing) |                       |              |

## EMC conformity and approvals

|               |  |                 |   |
|---------------|--|-----------------|---|
| EMC standards | EN 55032, EN 55024, CISPR 32, FCC Part 15B Class B, IEC 61000-4-2 ESD: Contact: 4 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 GHz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 V/m, IEC 61000-4-8 | Safety standard |   |
| Shock         | according to IEC 60068-2-27  | Vibration       | SELV according to EN 62368-1, UL 60950-1 according to IEC 60068-2-6 |
| Wireless      | EN 301 489-1/17, EN 300 328, EN 301893, TELEC, FCC ID SLE-WAPN008  |                 |   |

## Environmental conditions

|                             |                            |                             |       |
|-----------------------------|----------------------------|-----------------------------|-------|
| Humidity                    | 5 to 95 % (non-condensing) | Operating temperature, max. | 60 °C |
| Operating temperature, min. | 0 °C                       | Storage temperature, max.   | 85 °C |
| Storage temperature, min.   | -40 °C                     |                             |       |

## Guarantee

|               |         |
|---------------|---------|
| Time interval | 5 years |
|---------------|---------|

## Interfaces

|                                 |  |                        |  |
|---------------------------------|--|------------------------|--|
| Connector for external antennas | 2x RP-SMA female   | Console port interface | RS-232 (RJ45 connector)                                      |
| Function reset button           | Restoration of factory settings  | LED indicator          | PWR, FAULT, STATE, SIGNAL, WLAN, 10/100/1000M (TP-Port)      |
| RJ45 ports                      | 10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port | Standard antenna       | 2 dBi omni-directional dual band antenna, RP-SMA (male plug) |

## MTBF

|      |                              |                  |
|------|------------------------------|------------------|
| MTBF | According to Standard        | Telcordia SR-332 |
|      | Operating time (hours), min. | 749,476 h        |

Creation date July 16, 2024 9:21:07 PM CEST

## IE-WL-BL-AP-CL-EU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Power supply

|                             |  |      |  |
|-----------------------------|--|------|--|
| Connection type             | 1 removable 4-pin terminal block, 500 V insulation |      |  |
| Current consumption         | 0.56 A at 12 V DC, 0.14 A at 48 V DC               |      |  |
| Power consumption           | 6.96 W   |      |  |
| Reverse polarity protection | Available  |      |  |
| Voltage supply              | 24 V DC, 2 redundant inputs                        |      |  |
| Voltage supply range        | Voltage type                                       | DC   |  |
|                             | Voltage, min.                                      | 12 V |  |
|                             | Voltage, max.                                      | 48 V |  |

## Technical data

|                       |          |                   |      |
|-----------------------|----------|-------------------|------|
| Housing main material | metal    | Protection degree | IP30 |
| Type of mounting      | DIN rail |                   |      |

## Technology

|          |  |                     |   |
|----------|--|---------------------|---|
| Standard | IEEE 802.11 a/b/g/n for Wireless LAN, IEEE 802.11i for Wireless Security, IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3ab for 1000BaseT(X) | Supported protocols | Proxy ARP, DNS, HTTP, HTTPS, IP, ICMP, SNMP, TCP, UDP, Radius, SNMP, DHCP, LLDP |
|----------|--|---------------------|---|

## WLAN interface

|   |   |                |
|---|---|----------------|
| Data security                                   | SSID broadcast enable/disable, Firewall for MAC/IP/protocol/port-based filtering, 64-bit and 128-bit WEP encryption, WPA/WPA2 Personal and Enterprise (IEEE 802.1X/RADIUS, TKIP and AES)  |                |
| Operating channels (mid-band)                   | EU: 2.412 to 2.472 GHz (13 channels); 5.180 to 5.240 GHz (4 channels); 5.260 to 5.320 GHz (4 channels); 5.500 to 5.700 GHz (11 channels)  |                |
| Spreading code process and modulation (typical) | DSSS with DBPSK, DQPSK, CCK, OFDM with BPSK, QPSK, 16QAM, 64QAM, 802.11b: CCK at 11/5.5 MBit/s, DQPSK at 2 MBit/s, DBPSK at 1 MBit/s, 802.11a / g: 64QAM at 54/48 MBit/s, 16QAM at 36/24 MBit/s, QPSK at 18/12 MBit/s, BPSK at 9/6 MBit/s, 802.11n: 64QAM at 300 MBit/s to BPSK at 6.5 MBit/s   |                |
| Transmission rate                               | 802.11b: 1, 2, 5.5, 11 MBit/s, 802.11a/g: 6, 9, 12, 18, 24, 36, 48, 54 MBit/s, 802.11n: 6.5 to 300 MBit/s   |                |
| Transmission rate WLAN                          | Standard  | IEEE 802.11b   |
|   | max.  | 11 Mbps        |
|   | min.  | 1 Mbps         |
|   | Standard  | IEEE 802.11a/g |
|   | max.  | 54 Mbps        |
|   | min.  | 6 Mbps         |
|   | Standard  | IEEE 802.11n   |
|   | max.  | 300 Mbps       |
|   | min.  | 6.5 Mbps       |
| Transmit power                                  | 802.11b: type 26±1.5 dBm at 1 MBit/s, type 26±1.5 dBm at 2 MBit/s, type 26±1.5 dBm at 5.5 MBit/s, type 25±1.5 dBm at 11 MBit/s, 802.11g: type 23±1.5 dBm to 6 to 24 MBit/s, type 23±1.5 dBm at 36 MBit/s, type 19±1.5 dBm at 48 MBit/s, type 18±1.5 dBm at 54 MBit/s, 802.11a: type 23±1.5 dBm at 6 bis 24 MBit/s, type 21±1.5 dBm at 36 MBit/s, type 20±1.5 dBm at 48 MBit/s, type 18±1.5 dBm at 54 MBit/s, 802.11n (2.4 GHz): type 23±1.5 dBm at MCS0/8 20 MHz, type 18±1.5 dBm at MCS7/15 20 MHz, type 23±1.5 dBm at MCS0/8 40 MHz, type 17±1.5 dBm at MCS7/15 40 MHz, 802.11n (5 GHz): type 23±1.5 dBm at MCS0/8 20 MHz, type 18±1.5 dBm at MCS7/15 20 MHz, type 23±1.5 dBm at MCS0/8 40 MHz, type 17±1.5 dBm at MCS7/15 40 MHz |                |

## IE-WL-BL-AP-CL-EU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Wireless LAN receive sensitivity

802.11b: -93 dBm at 1 MBit/s, -93 dBm at 2 MBit/s, -93 dBm at 5.5 MBit/s, -88 dBm at 11 MBit/s, 802.11g: -88 dBm at 6 MBit/s, -86 dBm at 9 MBit/s, -85 dBm at 12 MBit/s, -85 dBm at 18 MBit/s, -85 dBm at 24 MBit/s, -82 dBm at 36 MBit/s, -78 dBm at 48 MBit/s, -74 dBm at 54 MBit/s, 802.11a: -90 dBm at 6 MBit/s, -88 dBm at 9 MBit/s, -88 dBm at 12 MBit/s, -85 dBm at 18 MBit/s, -81 dBm at 24 MBit/s, -78 dBm at 36 MBit/s, -74 dBm at 48 MBit/s, -72 dBm at 54 MBit/s, 802.11n (2.4 GHz): -70 dBm at MCS7 20 MHz, -69 dBm at MCS15 20 MHz, -67 dBm at MCS7 40 MHz, -67 dBm at MCS15 40 MHz, 802.11n (5 GHz): -69 dBm at MCS7 20 MHz, -71 dBm at MCS15 20 MHz, -63 dBm at MCS7 40 MHz, -68 dBm at MCS15 40 MHz

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000816    | ETIM 7.0    | EC000816    |
| ETIM 8.0    | EC000816    | ETIM 9.0    | EC000816    |
| ECLASS 9.0  | 19-17-02-01 | ECLASS 9.1  | 19-17-02-06 |
| ECLASS 10.0 | 19-17-05-01 | ECLASS 11.0 | 19-17-05-01 |
| ECLASS 12.0 | 19-17-05-01 | ECLASS 13.0 | 19-17-05-01 |

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 9229992a-00b9-4096-8962-200a7f33e289 |
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl                          |

## Approvals

|           |  |
|-----------|--|
| Approvals |     |
|-----------|--|

|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E230683    |

## Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">KC certificate</a><br><a href="#">EU Declaration of Conformity</a><br><a href="#">UK Declaration of Conformity</a>   |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Product Change Notification                 | <a href="#">Firmware Release Notes</a><br><a href="#">Product Change Notification IE-WL-BL-series</a>  |
| Software                                    | <a href="#">Software – WLAN Administration Tool</a><br><a href="#">Firmware – Firmware</a><br><a href="#">Device description – SNMP private MIB</a>                                  |
| User Documentation                          | <a href="#">Hardware Installation Guide</a><br><a href="#">Manual</a><br><a href="#">20210702 Security Advisory – Multiple vulnerabilities in Industrial WLAN devices (Update A)</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |