

**PRO COM IO-LINK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Weidmüller's plug-in communication modules enable individual components to exchange relevant data with the cloud. This lays the foundation for targeted process optimization using condition monitoring and remote controllability - factors that play a decisive role in increasing efficiency, quality, process stability and availability can contribute. The communication modules are designed according to IP20 protected, can be operated without tools and can be flexibly adapted to different customisable communication protocols.

**General ordering data**

General ordering data	
Version	Communication module
Order No.	<a href="#">2587360000</a>
Type	PRO COM IO-LINK
GTIN (EAN)	4050118599152
Qty.	1 pc(s).

## PRO COM IO-LINK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	33.6 mm	Depth (inches)	1.323 inch
Height	74.4 mm	Height (inches)	2.929 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	29 g		

## Temperatures

Operating temperature	-25 °C...70 °C
-----------------------	----------------

## General data

MTTF	According to Standard	SN 29500
	Operating time (hours), min.	7,148,000 h
	Ambient temperature	40 °C
	Duty cycle	100 %
Protection degree	IP20	
Weight	29 g	

## Connection data (signal)

Wire connection cross-section, flexible (signal), max.	1.5 mm <sup>2</sup>	Wire connection cross-section, flexible (signal), min.	0.14 mm <sup>2</sup>
Wire connection method	PUSH IN	Wire cross-section, AWG/kcmil , max.	16
Wire cross-section, AWG/kcmil , min.	26	Wire cross-section, solid , max.	1.5 mm <sup>2</sup>
Wire cross-section, solid , min.	0.14 mm <sup>2</sup>		

## Approbations

Certificate no. (cULus)	E258476	Certificate no. (cULusEX)	E470829
Institute (cULus)	CULUS	Institute (cULusEX)	CULUSEX

## Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-04-07-92
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-24-26-08	ECLASS 13.0	27-24-26-08

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	aa344edc-0272-47ae-a958-c5990fc92dd5
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl

## PRO COM IO-LINK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476
Certificate no. (cULusEX)	E470829

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">declaration of conformity</a> <a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a> <a href="#">Quick start guide – UR67-PN-HP-8IOL-12-60M Quick Start Guide for configuration of UR67-PN-IO-Link master</a> <a href="#">Compatibility of PRO COM</a>
Product Change Notification	<a href="#">PRO COM IO-LINK Release-Notes</a>
Software	<a href="#">Device description – IO-Link IODD für topGUARD</a> <a href="#">Device description – IO-Link IODD für PROtop</a> <a href="#">IO-Link IODD für PROtopDC</a>
User Documentation	<a href="#">Instruction sheet</a> <a href="#">IO-Link Register Description PROtop</a> <a href="#">IO-Link Register Description topGUARD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>