

**H0,75/16TS HBL BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Standard, 12 mm, 10 mm, Light Blue |
| Order No.  | <a href="#">2604660000</a>                           |
| Type       | H0,75/16TS HBL BD GSP                                |
| GTIN (EAN) | 4050118649468  |
| Qty.       | 4,000 pc(s).   |

## H0,75/16TS HBL BD GSP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 0.147 g |
|------------|---------|

## Technical data

|                        |  |         |          |
|------------------------|--|---------|----------|
| Description of article | Wire end ferrules on reel,<br>light blue | Version | Standard |
|------------------------|--|---------|----------|

## Wire-end ferrules

|                             |                      |  |               |
|-----------------------------|----------------------|--|---------------|
| Collar diameter (D2)        | 3.4 mm               | Colour code                                | Miscellaneous |
| Conductor cross-section     | 0.75 mm <sup>2</sup> | Contact surface diameter (D1)              | 1.2 mm        |
| Contact surface length (L2) | 10 mm                | L1 in mm                                   | 16 mm         |
| Metal sleeve thickness (S1) | 0.15 mm              | Plastic collar thickness (S2)              | 0.25 mm       |
| Stripping length            | 12 mm                | Wire connection cross section AWG,<br>max. | AWG 18        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ECLASS 9.0  | 27-40-02-01 | ECLASS 9.1  | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |
| ECLASS 14.0 | 27-40-02-01 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

## Approvals

Approvals



|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E354986    |

## Downloads

|                    |  |
|--------------------|--|
| User Documentation | <a href="#">Technical information - EN</a><br><a href="#">Technical information - DE</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>   |

**H0,75/16TS HBL BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Drawing**