


SDL 4 FT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Stud terminal, Threaded stud connection, 6 mm ² , 1000 V, 41 A, Number of connections: 2, M 4, TS 32, TS 35, grey
Order No.	2614970000
Type	SDL 4 FT
GTIN (EAN)	4050118654004
Qty.	50 pc(s).

SDL 4 FT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	51.5 mm	Depth (inches)	2.028 inch
Depth including DIN rail	52.2 mm	Height	86 mm
Height (inches)	3.386 inch	Width	11 mm
Width (inches)	0.433 inch	Net weight	18.3 g

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Polyamide	Colour	grey
----------	-----------	--------	------

System specifications

End cover plate required	Yes	Number of potentials	1
Number of levels	1	Number of clamping points per level	2
Number of potentials per tier	1	Levels cross-connected internally	No
PE connection	No	Rail	TS 32, TS 35
N-function	No	PE function	No
PEN function	No		

Additional technical data

Explosion-tested version	No	Open sides	right
Snap-on	Yes	Type of fixing	Snap-on
Type of mounting	TS 32, TS 35		

CSA rating data

Certificate number (cCSAus)	70198655	Wire cross section max. (cCSAusX)	8 AWG
Wire cross section min. (cCSAusX)	22 AWG		

SDL 4 FT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Conductors for clamping (rated connection)

2 x cable lugs DIN 46 234	1.5...6 mm ²	2 x cable lugs DIN 46 235	1.5...6 mm ²
Blade size	0.8 x 5.5 mm	Cable lug to DIN 46234	1.5...6 mm ²
Cable lug to DIN 46235	1.5...6 mm ²	Clamping range, bolted connection , max.	6 mm ²
Clamping range, bolted connection , min.	1.5 mm ²	Clamping range, max.	6 mm ²
Clamping range, min.	1.5 mm ²	Connection cross-section, stranded, max.	6 mm ²
Connection cross-section, stranded, min.	1.5 mm ²	Connection direction	on side
Number of connections	2	Stud size for spade connection	M 4
Tightening torque, max.	1.2 Nm	Tightening torque, min.	1.2 Nm
Type of connection	Threaded stud connection	Wire connection cross section AWG, max.	AWG 8
Wire connection cross section AWG, min.	AWG 22	Wire connection cross section, finely stranded, max.	6 mm ²
Wire connection cross section, finely stranded, min.	1.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	1.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	1.5 mm ²	Wire connection cross-section, solid core, max.	6 mm ²
Wire connection cross-section, solid core, min.	1.5 mm ²		

General

Rail	TS 32, TS 35	Standards	IEC 60947-7-1
Wire connection cross section AWG, max.	AWG 8	Wire connection cross section AWG, min.	AWG 22

Rating data

Rated cross-section	6 mm ²	Rated voltage	1,000 V
Rated DC voltage	1,000 V	Rated current	41 A
Standards	IEC 60947-7-1	Volume resistance according to IEC 60947-7-x	0.78 mΩ
Rated impulse withstand voltage	8 kV	Power loss in accordance with IEC 60947-7-x	1.31 W
Pollution severity	3		

UL rating data

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	8 AWG
Conductor size Factory wiring min. (cURus)	22 AWG	Conductor size Field wiring max. (cURus)	8 AWG
Conductor size Field wiring min. (cURus)	22 AWG	Current size B (cURus)	50 A
Current size C (cURus)	50 A	Voltage size B (cURus)	600 V
Voltage size C (cURus)	600 V		

SDL 4 FT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC000897	ETIM 7.0	EC000897
ETIM 8.0	EC000897	ETIM 9.0	EC000897
ECLASS 9.0	27-14-11-20	ECLASS 9.1	27-14-11-20
ECLASS 10.0	27-14-11-20	ECLASS 11.0	27-14-11-20
ECLASS 12.0	27-14-11-20	ECLASS 13.0	27-25-01-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E60693

Downloads

Approval/Certificate/Document of Conformity	CE Declaration of Conformity UKCA declaration of conformity
Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

SDL 4 FT

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



SDL 4 FT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	WS 12/9.5-11 MC NE WS	Version
Order No.	2484220000	, Polyamide 66, Colour: white
GTIN (EAN)	4050118494808	
Qty.	300 pc(s).	

SRL-Series



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Type	SQB 4/3	Version
Order No.	2615150000	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4050118653830	Pitch in mm (P): 11.00, Insulated: Yes, 41 A, black
Qty.	50 pc(s).	
Type	SQB 4/4	Version
Order No.	2615160000	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4050118653823	Pitch in mm (P): 11.00, Insulated: Yes, 41 A, black
Qty.	50 pc(s).	
Type	SQS 4/2	Version
Order No.	2615250000	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4050118653632	Pitch in mm (P): 11.00, Insulated: Yes, 41 A, black
Qty.	20 pc(s).	
Type	SQS 4/4	Version
Order No.	2615260000	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4050118653625	Pitch in mm (P): 11.00, Insulated: Yes, 41 A, black
Qty.	10 pc(s).	

Creation date June 5, 2024 10:33:17 PM CEST

SDL 4 FT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	SQBA 4/3	Version
Order No.	2615170000	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4050118653816	Pitch in mm (P): 22.00, Insulated: Yes, 41 A, black
Qty.	10 pc(s).	
Type	SRQB 4/2	Version
Order No.	2615220000	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4050118653663	Pitch in mm (P): 11.00, Insulated: Yes, 41 A, black
Qty.	100 pc(s).	
Type	SQB 4/2	Version
Order No.	2615140000	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4050118653847	Pitch in mm (P): 11.00, Insulated: Yes, 41 A, black
Qty.	100 pc(s).	
Type	SRQB 4/3	Version
Order No.	2615230000	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4050118653656	Pitch in mm (P): 11.00, Insulated: Yes, 41 A, black
Qty.	50 pc(s).	
Type	SRQB 4/4	Version
Order No.	2615240000	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4050118653649	Pitch in mm (P): 11.00, Insulated: Yes, 41 A, black
Qty.	50 pc(s).	
Type	SQBA 4/4	Version
Order No.	2615180000	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4050118653809	Pitch in mm (P): 22.00, Insulated: Yes, 41 A, black
Qty.	10 pc(s).	

Crimp cable lugs



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Type	KQI-M4/-1	Version
Order No.	1492200000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118302301	mm ²
Qty.	100 pc(s).	
Type	KQI-M4/-0,5	Version
Order No.	1492110000	cable lug, terminal end, Insulated cable connector, 0.5 mm ² , 0.1 mm ² -
GTIN (EAN)	4050118302103	0.5 mm ²
Qty.	100 pc(s).	
Type	KQI-M4/-2,5	Version
Order No.	1492290000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118302172	2.5 mm ²
Qty.	100 pc(s).	

Creation date June 5, 2024 10:33:17 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

SDL 4 FT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	KQI-M4/-6	Version
Order No.	1492370000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6 mm ²
GTIN (EAN)	4050118302264	
Qty.	100 pc(s).	

End plate**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Type	SEP SDL 4	Version
Order No.	2615020000	End plate (terminals), 86.1 mm x 1.5 mm
GTIN (EAN)	4050118653953	
Qty.	50 pc(s).	