

SQV 6/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Cross-connector (terminal), when screwed in, Number of poles: 2, Pitch in mm (P): 18.00, Insulated: No, 125 A, black, grey
Order No.	2615080000
Type	SQV 6/2
GTIN (EAN)	4050118653908
Qty.	100 pc(s).

SQV 6/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	32 mm	Depth (inches)	1.26 inch
Height	7.5 mm	Height (inches)	0.295 inch
Width	26 mm	Width (inches)	1.024 inch
Net weight	8.71 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	PA	Colour	black, grey
----------	----	--------	-------------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Type of fixing	when screwed in
Type of mounting	when screwed in		

Cross-connector

Rated current, multi-pole	125 A	Type	Cross-connector
---------------------------	-------	------	-----------------

Dimensions

Pitch in mm (P)	18 mm
-----------------	-------

General

Number of poles	2
-----------------	---

Rating data

Rated current	125 A
---------------	-------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Creation date June 5, 2024 3:54:48 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.