

PRO COM IO-LINK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller's plug-in communication modules enable individual components to exchange relevant data with the cloud. This lays the foundation for targeted process optimization using condition monitoring and remote controllability - factors that play a decisive role in increasing efficiency, quality, process stability and availability can contribute. The communication modules are designed according to IP20 protected, can be operated without tools and can be flexibly adapted to different customisable communication protocols.

General ordering data

| General ordering data | |
|-----------------------|----------------------------|
| Version | Communication module |
| Order No. | 2587360000 |
| Type | PRO COM IO-LINK |
| GTIN (EAN) | 4050118599152 |
| Qty. | 1 pc(s). |

PRO COM IO-LINK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 33.6 mm | Depth (inches) | 1.323 inch |
| Height | 74.4 mm | Height (inches) | 2.929 inch |
| Width | 35 mm | Width (inches) | 1.378 inch |
| Net weight | 29 g | | |

Temperatures

| | |
|-----------------------|----------------|
| Operating temperature | -25 °C...70 °C |
|-----------------------|----------------|

General data

| | | |
|-------------------|------------------------------|-------------|
| MTTF | According to Standard | SN 29500 |
| | Operating time (hours), min. | 7,148,000 h |
| | Ambient temperature | 40 °C |
| | Duty cycle | 100 % |
| Protection degree | IP20 | |
| Weight | 29 g | |

Connection data (signal)

| | | | |
|--|----------------------|--|----------------------|
| Wire connection cross-section, flexible (signal), max. | 1.5 mm ² | Wire connection cross-section, flexible (signal), min. | 0.14 mm ² |
| Wire connection method | PUSH IN | Wire cross-section, AWG/kcmil , max. | 16 |
| Wire cross-section, AWG/kcmil , min. | 26 | Wire cross-section, solid , max. | 1.5 mm ² |
| Wire cross-section, solid , min. | 0.14 mm ² | | |

Approbations

| | | | |
|-------------------------|---------|---------------------------|---------|
| Certificate no. (cULus) | E258476 | Certificate no. (cULusEX) | E470829 |
| Institute (cULus) | CULUS | Institute (cULusEX) | CULUSEX |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001604 | ETIM 7.0 | EC001604 |
| ETIM 8.0 | EC001604 | ETIM 9.0 | EC001604 |
| ECLASS 9.0 | 27-24-26-08 | ECLASS 9.1 | 27-04-07-92 |
| ECLASS 10.0 | 27-24-26-08 | ECLASS 11.0 | 27-24-26-08 |
| ECLASS 12.0 | 27-24-26-08 | ECLASS 13.0 | 27-24-26-08 |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | aa344edc-0272-47ae-a958-c5990fc92dd5 |
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl |

PRO COM IO-LINK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|---------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E258476 |
| Certificate no. (cULusEX) | E470829 |

Downloads


| | |
|---|---|
| Approval/Certificate/Document of Conformity | declaration of conformity Declaration of Conformity |
| Engineering Data | CAD data – STEP Quick start guide – UR67-PN-HP-8IOL-12-60M Quick Start Guide for configuration of UR67-PN-IO-Link master Compatibility of PRO COM |
| Product Change Notification | PRO COM IO-LINK Release-Notes |
| Software | Device description – IO-Link IODD für topGUARD Device description – IO-Link IODD für PROtop IO-Link IODD für PROtopDC |
| User Documentation | Instruction sheet IO-Link Register Description PROtop IO-Link Register Description topGUARD |
| Catalogues | Catalogues in PDF-format |

PRO COM IO-LINK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Slotted screwdriver**

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SDIS SLIM 0.6X3.5X100 | Version |
| Order No. | 2749610000 | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118896350 | thickness (A): 0.6 mm |
| Qty. | 1 pc(s). | |