

CB-DT 140/3.5 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

With our detectable marking solutions, we support our food and beverage industry customers in ensuring the high standards required within the HACCP concept. Due to a metallic filler, our detectable Cable Ties are identified reliably by metal and X-ray detectors. Identification minimises the risk of contamination during the food production process. MultiCards provide maximal safety because of properties like corrosion resistance. We regularly check and confirm the safety properties in our accredited laboratory. Actual colour may vary, the tone does not affect the product characteristics. Not suitable for direct contact with food.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler

General ordering data

| | |
|------------|---|
| Version | Cable ties, 3.5 x 140 mm, Polyamide 66, 180 N |
| Order No. | 2602760000 |
| Type | CB-DT 140/3.5 BL |
| GTIN (EAN) | 4050118650174 |
| Qty. | 100 pc(s). |

CB-DT 140/3.5 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Height | 140 mm | Height (inches) | 5.512 inch |
| Width | 3.5 mm | Width (inches) | 0.138 inch |
| Net weight | 0.65 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -25...85 °C |
|-----------------------------|-------------|

Installation materials

| | | | |
|-----------------------------------|--------------|---|--------------------------|
| Cable diameter, max. | 36 mm | Detectible in accordance with Rondotest | 0.3 mm Fe |
| For re-opening | No | Halogen | No |
| Material | Polyamide 66 | Operating temperature range, max. | 85 °C |
| Operating temperature range, min. | -25 °C | Recommended industries | Food processing industry |
| Tensile strength | 180 N | Tensile strength (Pound-force) | 40 lbf |
| UL 94 flammability rating | HB | UV-resistant | No |
| Version | Cable ties | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000046 | ETIM 7.0 | EC000046 |
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ECLASS 9.0 | 27-14-07-02 | ECLASS 9.1 | 27-14-07-02 |
| ECLASS 10.0 | 27-14-07-02 | ECLASS 11.0 | 27-14-07-02 |
| ECLASS 12.0 | 27-14-07-02 | ECLASS 13.0 | 27-14-07-02 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | CE Declaration of conformity |
| Catalogues | Catalogues in PDF-format |

CB-DT 140/3.5 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

