


SFX-DT 11/60 MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

We support our customers in the food industry with detectable marking solutions to ensure the high standards required within the framework of the HACCP concept. Thanks to a metallic filler, our detectable MultiCards can be reliably identified by metal and X-ray detectors. This minimises the risk of product contamination in the production process. Maximum safety is ensured with important product properties, such as corrosion resistance or higher ageing resistance to UV radiation in indoor areas and heat. These properties are regularly tested and confirmed in our own accredited laboratory. Not suitable for direct food contact.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler
- Clear and resistant print image
- Available in different versions for a wide variety of marking requirements

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | Conductor and cable markers, 7 - 40 mm, 60 x 11 mm, blue |
| Order No. | 2622430000 |
| Type | SFX-DT 11/60 MC SDR |
| GTIN (EAN) | 4050118623451 |
| Qty. | 12 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

SFX-DT 11/60 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.8 mm | Depth (inches) | 0.031 inch |
| Height | 60 mm | Height (inches) | 2.362 inch |
| Width | 11 mm | Width (inches) | 0.433 inch |
| Net weight | 1.831 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | |
|---|---|
| Colour | blue |
| Detectible in accordance with Rondotest | 4.7 mm Al |
| Halogen | No |
| Material | Polyamide 66 |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers |
| Number of markers per packaging unit | Form of supply MultiCard |
| Operating temperature range | -40...100 °C |
| Operating temperature range, max. | 100 °C |
| Operating temperature range, min. | -40 °C |
| Printed characters | To customer specification |
| Recommended industries | Food processing industry |
| Size of labelling field | 44 x 11 mm |
| UL 94 flammability rating | HB |
| Version | Installation with cable ties |
| Width | 11 mm |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D. | 7 - 40 mm | Conductor O.D., max. | 40 mm |
| Conductor O.D., min. | 7 mm | Conductor cross-section, max. | 500 mm ² |
| Conductor cross-section, min. | 16 mm ² | Cross-section for connected wire | 16 - 500 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

SFX-DT 11/60 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

