

POWERCRIMPER 6.0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The rationalisation of crimping processes calls for more and more automation of the individual steps. "Optimisation of installation times" is what the markets of the future will be demanding of their strategic partners. Automatic machines that permit rational processing of conductor materials represent the answer to an approach geared to future needs. Versatility and functionality are decisive factors for the customer. With our comprehensive line of automated machinery, Weidmüller provides professional and efficient solutions for cable preparation and processing.

General ordering data

| | |
|------------|---|
| Version | Crimping machine, 0.5mm ² , 6mm ² |
| Order No. | 2634310000 |
| Type | POWERCRIMPER 6.0 |
| GTIN (EAN) | 4050118660906 |
| Qty. | 1 pc(s). |

POWERCRIMPER 6.0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 405 mm | Depth (inches) | 15.945 inch |
| Height | 240 mm | Height (inches) | 9.449 inch |
| Width | 165 mm | Width (inches) | 6.496 inch |
| Net weight | 15,848 g | | |

Automatic crimping

| | | | |
|---------------------------------------|---------------------|---------------------------------------|---|
| Compressed-air connection | | Consumables | With and without plastic collar, Twin wire-end ferrules |
| | 5 - 5.5 bar | | |
| Crimping length | 6 - 18 mm | Crimping range | 0.5...6 mm ² |
| Crimping range, max. | 6 mm ² | Crimping range, min. | 0.5 mm ² |
| Drive | | Electrical connection | 100 - 240 V / 50/60 Hz / 16 VA |
| | Electropneumatic | | |
| Insertion length | | Note | Twin wire-end ferrules in the cross-section range from 2 x 0.5 to 2 x 2.5 mm ² , No need to change tools |
| | 13 | | |
| Pulse time | approx. 1 s | Wire end ferrules cross-section, max. | 6 mm ² |
| Wire end ferrules cross-section, min. | 0.5 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002778 | ETIM 7.0 | EC002778 |
| ETIM 8.0 | EC002778 | ETIM 9.0 | EC002778 |
| ECLASS 9.1 | 17-31-01-01 | ECLASS 10.0 | 17-13-01-01 |
| ECLASS 11.0 | 17-13-01-01 | ECLASS 12.0 | 17-13-01-01 |
| ECLASS 13.0 | 17-13-01-01 | | |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | d2df479e-2b79-4e98-adc7-b03577df98ae |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|--------------------|--|
| User Documentation | Manual |
| Catalogues | Catalogues in PDF-format |

POWERCRIMPER 6.0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

