

**PRO PM 75W 5V 14A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Due to the wide range of variants with output voltages of 5, 12, 24, and 48 V and extensive international approvals, they are suitable for use in many applications. The power range extends from 35 W to 350 W. The individual adaptability makes PRO-PM the right choice for many standard machines.

**General ordering data**

Version	Power supply, switch-mode power supply unit
Order No.	<a href="#">2660200281</a>
Type	PRO PM 75W 5V 14A
GTIN (EAN)	4050118782028
Qty.	1 pc(s).

## PRO PM 75W 5V 14A

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	99 mm	Depth (inches)	3.898 inch
Height	30 mm	Height (inches)	1.181 inch
Width	97 mm	Width (inches)	3.819 inch
Net weight	240 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...70 °C
Humidity	5...95 % RH		

## Input

AC current consumption	1 A @ 230 V AC / 2 A @ 115 V AC	
AC input voltage range	90...264 V AC	
Connection system	Screw connection	
Current consumption in relation to the input voltage	Voltage type	AC
	Input voltage	230 V
	Input current	1 A
	Voltage type	AC
	Input voltage	115 V
	Input current	2 A
Frequency range AC	47...63 Hz	
Inrush current	max. 45 A	
Nominal power consumption	91.5 VA	
Rated input voltage	100...240 V AC	
Recommended back-up fuse	4 A at 230 V AC, characteristic curve C	

## Output

Connection system	Screw connection	Mains failure bridge-over time	20 ms
Output power		Output voltage, note	± 10% nominal output voltage tolerance, adjustable with potentiometer
	75 W		
Overload protection	120%...180% I <sub>nominal</sub> , hiccup mode with automatic recovery	Parallel connection option	Yes, with diode module
Rated current	14 A	Rated output voltage	5 V DC
Residual ripple, breaking spikes	< 100 mV <sub>pp</sub>	Surge protection	5.6...6.8 V @ 5 V DC

## General data

Degree of efficiency	82 %	Derating	> 50°C (2% / 1°C)
Humidity	5...95 % RH	Mounting position, installation notice	Panel mount, screw fix
Protection degree	IP20	Short-circuit protection	Yes
Status indication	LED green: ready		

## PRO PM 75W 5V 14A

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## EMC / shock / vibration

Interference immunity test acc. to	Burst: EN 61000-4-4 / ESD EN 61000-4-2, EN61000-4-3 (HF field), EN 61000-4-5 (surge), EN 61000-4-6 (conducted), EN61000-4-8 (Fields), EN 61000-4-11 (Dips)	Noise emission in accordance with EN55032	
Shock resistance IEC 60068-2-27	30 g in all directions	Vibration resistance IEC 60068-2-6	Class B 10...500 Hz, constant ac- celeration 5 g, 10 min- utes/cycle, 60 minutes/ax- is

## Insulation coordination

Insulation voltage input / earth	2 kV	Insulation voltage output / earth	0.5 kV
Insulation voltage, input/output	3 kV		

## Electrical safety (applied standards)

Safety extra-low voltage	SELV acc. to IEC 60950-1, PELV according to EN 60204-1
--------------------------	--

## Connection data (input)

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	21
Conductor cross-section, rigid , max.	4 mm <sup>2</sup>	Conductor cross-section, rigid , min.	0.34 mm <sup>2</sup>
Connection system	Screw connection		

## Connection data (output)

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	21
Conductor cross-section, rigid , max.	4 mm <sup>2</sup>	Conductor cross-section, rigid , min.	0.34 mm <sup>2</sup>
Connection system	Screw connection		

## Signalling

Status indication	LED green: ready
-------------------	------------------

## Classifications

ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ETIM 9.0	EC002540
ECLASS 9.0	27-04-07-01	ECLASS 9.1	27-04-07-01
ECLASS 10.0	27-04-07-01	ECLASS 11.0	27-04-07-01
ECLASS 12.0	27-04-07-01	ECLASS 13.0	27-04-07-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Lead oxide 1317-36-8
SCIP	015c3a09-4dd7-4b84-85e2-16a46fa4e79a

## PRO PM 75W 5V 14A

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of Conformity [PRO PM 75W UL 62368.pdf Declaration of Conformity](#)

Engineering Data [CAD data – STEP](#)

User Documentation [Instruction sheet](#)

Catalogues [Catalogues in PDF-format](#)