

**SAIBC-5-18/28-4/9CG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The crimp connection is characterised by high functional reliability. With this connection technology, the conductor is crimped to the contact and then engaged in the contact carrier. The connection between the conductor and crimp is vibration-resistant and boasts long-term stability. Crimp contacts are to be ordered separately.

**General ordering data**

Version	Field attachable connector, M12, Female socket, straight
Order No.	<a href="#">2664800000</a>
Type	SAIBC-5-18/28-4/9CG
GTIN (EAN)	4050118765250
Qty.	1 pc(s).

## SAIBC-5-18/28-4/9CG

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	20.5 g
------------	--------

## Technical data customisable plug-in connectors

Cable diameter	4...9 mm	Cable diameter, max.	9 mm
Cable diameter, min.	4 mm	Coding	A-coded
Conductor cross-section, max.	0.75 mm <sup>2</sup>	Conductor cross-section, min.	0.08 mm <sup>2</sup>
Contact surface	Gold-plated	Housing main material	CuZn
Number of poles	5	Plugging cycles	≥ 500
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	50 V
Shield connection	Yes	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Brass, nickel-plated	Type of connection	Crimp connection

## General Info

Number of poles	5	Connection 1	M12
Connection 2	Crimp	Housing main material	CuZn
Connection thread	M12	Contact surface	Gold-plated
Protection degree	IP67	Plugging cycles	≥ 500

## Standards

Connector standard	IEC 61076-2-101	Fire safety for railway vehicles	According to EN 45545, HL1 - HL3
Shock and vibration proof according to	DIN EN 61373 KAT2 (Bogie), DIN EN 61373 Class 1B**		

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4
RoHS Compliance Status	Compliant

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**


**SAIBC-5-18/28-4/9CG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**


**Dimensioned drawing**



**Dimensioned drawing**



**Pole scheme**



## SAIBC-5-18/28-4/9CG

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Crimp contacts



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The crimp connection is characterised by high functional reliability. With this connection technology, the conductor is crimped to the contact and then engaged in the contact carrier. The connection between the conductor and crimp is vibration-resistant and boasts long-term stability.

Crimp contacts are to be ordered separately.

## General ordering data

Type	SAI-M12-KBC-22/24	Version
Order No.	<a href="#">2673730000</a>	Contact, Socket connector
GTIN (EAN)	4050118754599	
Qty.	100 pc(s).	
Type	SAI-M12-KBC-20/22	Version
Order No.	<a href="#">2664870000</a>	Contact, Socket connector
GTIN (EAN)	4050118755213	
Qty.	100 pc(s).	
Type	SAI-M12-KBC-26/28	Version
Order No.	<a href="#">2673740000</a>	Contact, Socket connector
GTIN (EAN)	4050118755084	
Qty.	100 pc(s).	
Type	SAI-M12-KBC-18/20	Version
Order No.	<a href="#">2664860000</a>	Contact, Socket connector
GTIN (EAN)	4050118755206	
Qty.	100 pc(s).	

**Data sheet****SAIBC-5-18/28-4/9CG****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Accessories****...for M12**

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

**General ordering data**

Type	SAI-TMCSK	Version
Order No.	<a href="#">1381690000</a>	Pressing tool, 4-indent crimp
GTIN (EAN)	4050118183870	
Qty.	1 pc(s).	