

VPCB PV II 1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

'Abbildung ähnlich'

Versatile accessories round off the surge protection range. E.g. the all-purpose measuring device V-TEST, which is used to check the function of pluggable arresters such as VSPC.

General ordering data

Order No.	2665680000
Type	VPCB PV II 1000
GTIN (EAN)	4050118686630
Qty.	20 pc(s).

VPCB PV II 1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	52.2 mm	Depth (inches)	2.055 inch
Height	61.6 mm	Height (inches)	2.425 inch
Width	17.9 mm	Width (inches)	0.705 inch
Net weight	10 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

General data

Colour	grey	Design	miscellaneous
Protection degree	IP20	UL 94 flammability rating	V-0
Version	Miscellaneous		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Conditions and requirements	EN 50539-11	Discharge current I_n (8/20 μ s)	20 kA
Discharge current, max. (8/20 μ s)	40 kA	Operating height in the grounded PV system	≤ 4000 m
PV system voltage, max. U_{cpv}	1,500 V	Requirements class	Type I/II
Short-circuit current I_{scpv}	11 kA		

Rated data IEC / EN

Discharge current, max. (8/20 μ s)	40 kA	Number of poles	1
Voltage type	DC		

Connection data

Type of connection	Solder connection, when screwed in
--------------------	------------------------------------

Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

VPCB PV II 1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
User Documentation	Assembly instructions VPCB PV
Catalogues	Catalogues in PDF-format


VPCB PV II 1000

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Similar to illustration




Dimensioned drawing




Example of use



Electric symbol



Schematic circuit diagram



Application with arrestor

Bestellnummer / Order number / Numéro de commande / Numero dell'ordine / Número de pedido / 订货号	Bezeichnung / Designation / Désignation / Designazione / Designación / 规格	Bestellnummer / Order number / Numéro de commande / Numero dell'ordine / Número de pedido / 订货号	Bezeichnung / Designation / Désignation / Designazione / Designación / 规格
254300000	VPCB PV II 1000	250600000	VPU PV II 0 1000
254300000	VPCB PV II 0 1000 1)	250600000	VPU PV II 0 1000
254300000	VPCB PV II 0 1000 1)	250600000	VPU PV II 0 1000
254300000	VPCB PV II 0 1000 1)	250600000	VPU PV II 0 1000
254300000	VPCB PV II 0 1000 1)	250600000	VPU PV II 0 1000

1) R = Fernmeldeanlage / Remote signaling contacts / Contactos de señalización remota / Contatti di segnalazione remota / Contactos de señalización a distancia / 远端信号触点

Selection

VPCB PV II 1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Spare Arrester****General ordering data**

Type	VPU PV II 0 1000	Version
Order No.	2530660000	Surge voltage arrester, Low voltage, Accessories, Spare arrester
GTIN (EAN)	4050118540871	
Qty.	9 pc(s).	