

IE-SR-2TX-WL-4G-EU**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Weidmüller Industrial Security Routers**

- Secure networks
 - Stateful packet inspection Firewall
 - IP/Port- forwarding
 - Network segmentation
- Easy integration of machine networks into manufacturing networks through 1: 1 NAT
- Secure and easy remote maintenance with Weidmüller u-link remote access service
- Enable modular and future proof network architectures with static and dynamic routing
- Secure communication over the Internet by using IPsec and OpenVPN
- Reliable internet connection, even without on-site internet access, thanks to integrated 4G/LTE cellular modem
- Full flexibility thanks to Fast Ethernet and Gigabit Ethernet interfaces ranging from 2 up to 4 ports.

General ordering data

Version	Security/NAT/VPN/U-link Router, with integrated multi-band modem (4G/3G/2G), EU-model, Fast Ethernet, 2x RJ45 10/100BASE-T(X), 1x DB9 male for RS-232/422/485, IP30, -25 °C...70 °C
Order No.	2682560000
Type	IE-SR-2TX-WL-4G-EU
GTIN (EAN)	4050118692150
Qty.	1 pc(s).

IE-SR-2TX-WL-4G-EU

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	81 mm	Depth (inches)	3.189 inch
Height	95 mm	Height (inches)	3.74 inch
Width	45 mm	Width (inches)	1.772 inch
Net weight	437 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Humidity	5 to 95 % (non-condensing)		

Mobile radio interface

Frequency band	LTE-FDD: B1, B3, B7, B8, B20, B28A, LTE-TDD: B38, B40, B41, WCDMA: B1,B8, GSM: B3,B8		
Transmission rate mobile radio	LTE category	CAT 4	
	Download rate, max.	150 Mbit/s	
	Upload rate, max.	50 Mbit/s	
Wireless module	multi-band modem (4G/3G/2G), Region: EMEA		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 4 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz bis 1 GHz: 3 V/m, IEC 61000-4-4 EFT: Power: 0.5 kV; Signal: 0.5 kV, IEC 61000-4-5 Surge: Power: 0.5 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 Vrms	Free fall	
Safety standard	SELV according to EN 62368-1, UL 61010-1, UL 61010-2-201	Shock	According to IEC 60068-2-31
Vibration	according to IEC 60068-2-6		according to IEC 60068-2-27

Environmental conditions

Humidity	5 to 95 % (non-condensing)	
Operating altitude	Altitude, max.	2,000 m
	Note	in acc. with UL
	Altitude, max.	6,000 m
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads
Operating temperature, max.	70 °C	
Operating temperature, min.	-25 °C	
Storage temperature, max.	85 °C	
Storage temperature, min.	-40 °C	

Guarantee

Time interval	5 years
---------------	---------

IE-SR-2TX-WL-4G-EU**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Interfaces**

Connector for external antennas	2x SMA female, 1x RP-SMA female	Digital inputs	1x, 5 to 30 V for logic "1", 0 to 2 V for logic "0"
Digital outputs	1x, with a current capacity of 0.2 A at 30 V DC	Function reset button	<5 sec: System reboot and set LAN IP to factory Default, >5 sec: Factory default
Number of SIM-Card slots	2	Number of ports	2x RJ45 10/100BASE-T(X), 1x DB9 male for RS-232/422/485
SIM-Card slot type	Mini-SIM (ID-000 format)		

MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	355,921 h

Management features

Device configuration	Webbrowser (HTTP/HTTPS), SNMP v2c, Command Line Interface (Telnet/SSH), Upload of a configuration file via web-interface, SMS control commands	Monitoring function	SNMP v2c, Syslog, Event based warning via E-Mail, Event based warning via relay, Event based warning via SNMP trap, Event based warning via SMS, Device information and mobile radio status via SMS request
IP-address management	Static, DHCP-Client, DHCP-Server (pool-based), DHCP-Relay, DNS-Relay	Security functions	Access Control List (MAC-based) for WLAN Access Point mode
Time synchronization management	NTP server, NTP client	Operating modes	WLAN Access Point, WLAN Client, Virtual COM mode, TCP Server mode, TCP Client mode, UDP Server/Client mode

Power supply

Connection type		1 removable 4-pin terminal block	
Current consumption	Voltage	12 V	
	Current	0.46 A	
	Voltage	24 V	
	Current	0.22 A	
	Voltage	48 V	
	Current	0.11 A	
Overload current protection		Yes	
Reverse polarity protection		Yes	
Voltage supply		12/24/48 V DC, 2 redundant inputs, or 48 V DC Power-over-Ethernet (IEEE 802.3af)	
Voltage supply range	Voltage type	DC	
	Voltage, min.	10.8 V	
	Voltage, max.	52.8 V	

IE-SR-2TX-WL-4G-EU

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Routing Features

Firewall functions	Stateful Packet Inspection Firewall (Layer-3)	NAT functions	Source / Destination NAT (Port / Host / Network)
Routing functions	IPv4 routing, Static and dynamic IP Routing	VPN functions	u-link client, OpenVPN (Server or Client), IPSec (Initiator or Responder)

Serial communication parameters

Baud rate	110 bit/s to 460800 bit/s	Data bits	7, 8
Parity	none, odd, even, Mark, Space	Stop bits	1, 2

Technical data

Housing main material	Metal	Protection degree	IP30
Speed	Fast Ethernet	Type of mounting	DIN rail, Wall mounting

Technology

Standard	IEEE 802.3 for 10BASE-T, IEEE 802.3u for 100BASE-TX, IEEE 802.3af for Power-over-Ethernet, IEEE 802.11b/g/n for Wireless LAN
----------	---

WLAN interface

Data security	64-bit and 128-bit WEP encryption, WPA/WPA2 Personal and Enterprise (IEEE 802.1X/RADIUS, TKIP and AES)		
Transmission rate WLAN	Standard	IEEE 802.11b	
	max.	11 Mbit/s	
	min.	1 Mbit/s	
	Standard	IEEE 802.11g	
	max.	54 Mbit/s	
	min.	6 Mbit/s	
	Standard	IEEE 802.11n	
	max.	150 Mbit/s	
	min.	6.5 Mbit/s	

Classifications

ETIM 6.0	EC001478	ETIM 7.0	EC001478
ETIM 8.0	EC001478	ETIM 9.0	EC001478
ECLASS 9.0	19-17-01-03	ECLASS 9.1	19-17-01-03
ECLASS 10.0	19-17-04-05	ECLASS 11.0	19-17-04-05
ECLASS 12.0	19-17-04-05	ECLASS 13.0	19-17-04-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Important note

Product information	Not compatible with the SCM card IE-EBR-SMARTCARD-SR 2909820000.
---------------------	--

Creation date June 3, 2024 8:37:22 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

IE-SR-2TX-WL-4G-EU**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity UK Declaration of Conformity RCM Declaration of Conformity Manufacturer's declaration for operating altitude
Engineering Data	CAD data – STEP
Product Change Notification	Firmware Release Notes ComServer/Modbus-Gateway Utility Release Notes
Software	Software – u-link VPN-Client Software – ComServer/Modbus-Gateway Utility (Virtual COM Port Driver) Firmware – Current Firmware
User Documentation	u-link EULA V3 EN (28.5.2018) Hardware Installation Guide User manual u-link EULA V4 EN (20.9.2023) Mandatory connection parameters for u-link VPN clients
Catalogues	Catalogues in PDF-format

IE-SR-2TX-WL-4G-EU**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Mounting kit for 19" rack assembly**

- For assembling DIN rail-based devices on 19" racks

**General ordering data**

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

IE-SR-2TX-WL-4G-EU

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

u-link Remote Access Service



The Weidmüller u-link remote access service offers an easy possibility to securely access ethernet devices in a remote network.

With the u-link VPN Server as the central meeting point server, the VPN clients (service PC and Weidmüller u-link client devices) always connect outbound and thus conform to the typical IT security requirements. Separate database and server instances are used for each u-link customer account (secure client isolation) to ensure data integrity.

Communication between the u-link VPN server and remote clients (service PCs and u-link client devices) takes place via a certificate-protected openVPN connection. The u-link creed is "configuration instead of programming" the use is intuitive and does not require expert knowledge.

Featureset:

- 1-click VPN remote access for service PC's
- easyAccess: web, rdp or vnc connections to remote hosts fully browser based for use with tablet or smartphone
- Organization and Group Management
- Topologies including 3rd party end-devices
- Firmware management: Display of firmware status of all routers and the option of a time-controlled, automated firmware update
- Individual access rights: granular configuration of access rights to devices in the target network
- Extensive event log: Presentation of all activities in the u-link portal with extensive filter and export functions
- Password policy: Increased security through configurable specification of minimum requirements for password quality and validity period

Weidmüller offers the following usage variations and additional options for the u-link Remote Access Service:

Basic version:

- Automatically assigned by registering at u-link.weidmueller.com
- Free use for 6 months, extended to 365 days when registering a new u-link client device
- Full featureset
- Unlimited users
- Max. 50 u-link capable devices (access points to a remote network)
- 1 simultaneous VPN connection
- No data or speed limitations (subject to normal market usage)

Extensions

- Additional 50/100/250/500/1000 or more u-link capable devices
- Additional simultaneous VPN connections
- China-VPN: secure and reliable VPN connection to and from China

General ordering data

Type	U-LINK-50-DEVICES-1Y	Version
Order No.	2status01.06.2024 / We reserve the right to make technical changes.	
GTIN (EAN)	configurable u-link clients on Weidmüller hardware to the basic	

IE-SR-2TX-WL-4G-EU

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	U-LINK-1-CONNECTION-1Y	Version
Order No.	2870130000	"VPN connection" licence code for u-link Remote Access Service. Can
GTIN (EAN)		be used as an additional VPN connection or to extend the period of a
Qty.	1 pc(s).	VPN connection that has already been activated
Type	U-LINK-100-DEVICES-1Y	Version
Order No.	2870100000	License code for u-link Remote Access Service., Adds 100 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 pc(s).	license and extends the period of the basic license accordingly.
Type	U-LINK-1000-DEVICES-1Y	Version
Order No.	2924220000	License code for u-link Remote Access Service., Adds 1000 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 pc(s).	license and extends the period of the basic license accordingly.
Type	U-LINK-500-DEVICES-1Y	Version
Order No.	2870120000	License code for u-link Remote Access Service., Adds 500 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 pc(s).	license and extends the period of the basic license accordingly.
Type	U-LINK-CNSERVER-1Y	Version
Order No.	2870140000	License code for u-link Remote Access Service., Allows the use of the
GTIN (EAN)		server in China for a secure and reliable VPN connection to and from
Qty.	1 pc(s).	China.
Type	U-LINK-BASIC-EXTENSION- ...	Version
Order No.	3024610000	License code for u-link Remote Access Service., Extends the period of
GTIN (EAN)		the basic license by 1 year.
Qty.		
Type	U-LINK-250-DEVICES-1Y	Version
Order No.	2870110000	License code for u-link Remote Access Service., Adds 250 additional
GTIN (EAN)		configurable u-link clients on Weidmüller hardware to the basic
Qty.	1 pc(s).	license and extends the period of the basic license accordingly.

Antennas and antenna accessories (coax cables and mounts)



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Type	IE-ANT-CELL-MIMO-DO-SMAM	Version
Order No.	2788120000	Omni-directional antenna, Cellular antenna, Up to 5G (NR), Linear,
GTIN (EAN)	4064675066385	Vertical, 2x SMA male, IP67, Impedance: 50 Ω
Qty.	1 pc(s).	
Type	IE-ANT-CELL-SISO-EO-SMAM	Version
Order No.	2788130000	Omni-directional antenna, Cellular antenna, Up to 5G (support for
GTIN (EAN)	4064675066392	frequencies below 2.7 GHz, e.g., bands n1, n2, n28), Vertical, SMA
Qty.	1 pc(s).	male, IP66, Impedance: 50 Ω

Creation date June 3, 2024 8:37:22 PM CEST

IE-SR-2TX-WL-4G-EU**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	IE-ANT-CELL/WL-MB-MIMO- ...	Version
Order No.	2788090000	Omni-directional antenna, Cellular antenna, Wi-Fi antenna, Up to 5G
GTIN (EAN)	4064675066354	(NR), Up to Wi-Fi 6 & 6E (IEEE802.11ax), Linear, Vertical, 2x SMA
Qty.	1 pc(s).	male, 2x RP-SMA male, IP67, Impedance: 50 Ω
Type	IE-ANT-WL-DB-SISO-LO-NF	Version
Order No.	2788110000	Omni-directional antenna, Wi-Fi antenna, Up to Wi-Fi 6 & 6E
GTIN (EAN)	4064675066378	(IEEE802.11ax), Vertical, N female, IP67, Impedance: 50 Ω
Qty.	1 pc(s).	
Type	IE-ANT-P-ABG-75-9-NF	Version
Order No.	1367140000	WLAN antenna, Directional antenna, Dual Band (2.4 GHz / 5 GHz),
GTIN (EAN)	4050118186338	Gain 9 dBi, Vertical, 1x N-type female, bottom, IP67, Impedance: 50 Ω
Qty.	1 pc(s).	