

**VG M12 EXE 4-6.5 SI7J G4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety).

Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, they are ATEX and IECEx certified.

**General ordering data**

Version	VG Exe 7J (Ex plastic cable gland 7J Exe), Cable glands, straight, M 12, 10 mm, OD min. 4 - OD max. 6.5 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">2722070000</a>
Type	VG M12 EXE 4-6.5 SI7J G4
GTIN (EAN)	4050118821307
Qty.	100 pc(s).

## VG M12 EXE 4-6.5 SI7J G4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	28.3 mm	Height (inches)	1.114 inch
Length	22 mm	Length (inches)	0.866 inch
Net weight	4 g		

## Temperatures

Operating temperature	-60 °C...70 °C
-----------------------	----------------

## Certificate numbers cable gland

Approval conditions	ATEX, IECEX	Identification	Ex eb IIC Gb, Ex tb IIIC Db IP66/68
---------------------	-------------	----------------	--

## General information

AF size 1	15 mm	AF size 2	15 mm
Cable glands	metric	Explosion protection type	Improved safety Ex e
External thread	M 12	Halogen	No
Impact resistance	7 joules in acc. with IEC 60079-0	Installation guidelines	See assembly instructions
Length of thread	10 mm	Material	Polyamide 6
Operating temperature range, max.	70 °C	Operating temperature range, min.	-60 °C
Outer cable diameter, max.	6.5 mm	Outer cable diameter, min.	4 mm
Pitch of thread	1.5 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Seal insert	Silicone
Sealing	Silicone	Standards	IEC 60079-0, EN 60079-0, IEC 60079-7, EN 60079-7, EN 60079-31, IEC 60079-31
Tightening torque	2 Nm	Torque for cap nut, max.	2.5 Nm
Torque for cap nut, min.	1.5 Nm	Torque for connecting adapter, max.	2.5 Nm
Torque for connecting adapter, min.	1.5 Nm	UL 94 flammability rating	HB

## Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-34
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-02	ECLASS 13.0	27-14-08-02
ECLASS 14.0	27-14-08-02		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

Approvals	CE; EAC; ATEX; IECEX; INMETRO
ROHS	Conform

### VG M12 EXE 4-6.5 SI7J G4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

**VG M12 EXE 4-6.5 SI7J G4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Plastic lock nuts, black**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	SKMU M12 K SW	Version
Order No.	<a href="#">1806540000</a>	SKMU PA (plastic locknut), Locknut, M 12, 5 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4032248276493	GF30)
Qty.	100 pc(s).	