

PB-CON IKSC M4X8 A2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Future-proof design
- Different module sizes
- Simple device integration
- Simple plug-and-play solution – fast replacement of individual modules from a single device network
- Quick and easy installation without tools
- Safe locking of busbar connectors
- Touch-safe construction
- Tolerance compensation in the rail system allows simple mounting of the devices on the panel mounting plate without extreme accuracy
- Uncomplicated UL approval with registered UL components
- Ideal design of size and technical data for typical multi-axis servo amplifiers

General ordering data

Version	PCB plug-in connector, Mounting screw
Order No.	2708610000
Type	PB-CON IKSC M4X8 A2
GTIN (EAN)	4050118775464
Qty.	40 pc(s).
Product data	

PB-CON IKSC M4X8 A2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	1.56 g
------------	--------

Material data

Insulating material	Steel	Contact material	Cu-alloy
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C
Operating temperature, min.	-50 °C	Operating temperature, max.	100
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984
-------------------------	------------------------

Packing

VPE length	80 mm	VPE width	43 mm
VPE height	17 mm		

Classifications

ETIM 6.0	EC000887	ETIM 7.0	EC000887
ETIM 8.0	EC003861	ETIM 9.0	EC003861
ECLASS 9.0	23-11-01-90	ECLASS 9.1	23-11-01-90
ECLASS 10.0	23-11-01-90	ECLASS 11.0	23-11-01-90
ECLASS 12.0	23-11-01-90	ECLASS 13.0	23-11-01-90

Important note

IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.
----------------	--

Notes	<ul style="list-style-type: none">Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months
-------	--

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--