

**HSS 1.6-4.8 EL W100M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Order No.	<a href="#">2724710000</a>
Type	HSS 1.6-4.8 EL W100M
GTIN (EAN)	4050118819328
Qty.	1 pc(s).

**HSS 1.6-4.8 EL W100M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.77 mm	Depth (inches)	0.03 inch
Width	7.6 mm	Width (inches)	0.299 inch
Length	100,000 mm	Length (inches)	3,937 inch
Net weight	570 g		

**General data**

Colour	white	Halogen	Yes
Length	100,000 mm	Material	Polyolefine
Operating temperature range, max.	135 °C	Operating temperature range, min.	-55 °C
Printed characters	without	Type of printing	neutral
Width	7.6 mm		

**Conductor and cable markers**

Conductor O.D., max.	4.8 mm	Conductor O.D., min.	1.6 mm
Conductor cross-section, max.	4 mm <sup>2</sup>	Conductor cross-section, min.	0.75 mm <sup>2</sup>
Halogen	Yes		

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	------------------------------------------