

TS 35X7.5/1.0 2M/CU/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Copper has the best electrical conductivity of all metals used. The copper rail has the highest short-circuit protection.

General ordering data

Version	Terminal rail, Accessories, 35 x 7.5 x 2000 mm, Copper, untreated
Order No.	2731380000
Type	TS 35X7.5/1.0 2M/CU/BK
GTIN (EAN)	4050118810882
Qty.	2 m

TS 35X7.5/1.0 2M/CU/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	540 g		

Mounting rail

Length of the terminal rail	max.	2,000 mm
	min.	0 mm
	nominal	2,000 mm
Material	Copper	
Permitted thermal current for PEN function, max.	150 A	
Pre-punched mounting rail	No	
Short circuit strength corresponds to E-Cu wire	50 mm²	
Short-time withstand current per second 6 kA according to IEC 60947-7-2		
Slit gap		
Slit length		
Slit width		
Standards	DIN EN 60715	
Surface finish	untreated	
Thickness	1 mm	

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

TS 35X7.5/1.0 2M/CU/BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

